










REV.	DATE	DESCRIPTION
NC	01/20/03	INITIAL RELEASE



- NOTE:
1. CRIMPED FERRULE
HEX CRIMP SIZE .178"
 2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"

9	FERRULE	COPPER	NICKEL	1	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	DO NOT SCALE DRAWING	CAD FILE C:/122/122192.DWG	DWG. NO. 122192.DWG	REV. NC	SIZE A	SCALE NA
8	SLEEVE	DELRIIN	NATURAL	1							
7	HEX NUT	BRASS	NICKEL	1							
6	LOCK WASHER	BRASS	NICKEL	1							
5	CONTACT PIN	PHOS. BRONZE	GOLD	1							
4	GASKET	RUBBER	RED	1							
3	BARREL	BRASS	NICKEL	1							
2	INSULATOR	DELRIIN	NATURAL	1							
1	HOUSING/BODY	BRASS	NICKEL	1							
DESCRIPTION		MATERIAL		FINISH		QTY					
					APPROVALS		DATE				
					DRAWN G.R.S.		01/20/03				
					CHECKED						
					ISSUED						
					SHEET 1 OF 1						
					PART NO.		122192				
					PART DESCRIPTION TNC BULKHEAD CRIMP JACK (FOR RG174/u, 188A/u, 316/u CABLE)						

Amphenol Connex

TNC BULKHEAD CRIMP JACK
(FOR RG174/u, 188A/u, 316/u CABLE)

122192