




FIG 1




FIG 2




FIG 3




FIG 4




FIG 5

Figure	Nylon 6/6 25% Glass Filled UL94 V-0 RMS-112 Colour: Black	Nylon 6/6 UL94 V-0, RMS-19 Colour: Black	Nylon 6/6 UL94 V-0, RMS-19 Colour: Natural	Nylon 6/6 UL94 V-2, RMS-01 Colour: Natural	Nylon 6/6 UL94 V-2, RMS-01 Colour: Black	Hole Diameter ± .08 (.003)	Panel Thickness
1	SPECIAL BPF-A414-GF	STANDARD BPF-A414	SPECIAL BPF-A414-19NT	-	-	4.7 [.185]	0.8 - 3.0 [.031 - .118]
2	-	SPECIAL BPF-F4410-19	-	SPECIAL BPF-F4410NT	STANDARD BPF-F4410	5.0 [.197]	1.5 - 7.5 [.059 - .295]
3	-	STANDARD BPF-F2495	-	-	-	7.0 [.276]	3.2 - 6.0 [.125 - .236]
4	-	STANDARD BPF-F3T31	-	-	-	5.0 [.197]	2.0 - 10.0 [.079 - .394]
5	SPECIAL BPF-F1G12-GF	STANDARD BPF-F1G12	-	-	-	7.0 [.276]	2.0 - 15.0 [.079 - .591]

REV	MODIFICATION	DATE	DRN
01	DRAWING RELEASE ECN 06-229	05/10/06	NJB
02	ECN 06-233	11/10/06	NJB
03	CO2010372	03/09/08	SF
04	CO2010405	23/09/08	TC
05	CO2010642	01/05/09	SF

NOTE


- 1) OTHER COLOURS AVAILABLE BY SPECIAL ORDER.
EXAMPLE: BPF-A414-OR FOR ORANGE.

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO
RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR
REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.



GENERAL TOLERANCES ±0.25 [.010]
UNLESS OTHERWISE STATED
1 DECIMAL PLACE ± 0.25 [.010]
2 DECIMAL PLACES ± 0.10 [.004]
ANGULAR ±1°

THIRD
ANGLE



MATERIAL: SEE TABLE				COLOUR: SEE NOTE	
DESCRIPTION: Barbed Push Fastener				PART No: SEE TABLE	
DRG No: 06-045		NPR No:			SHEET SIZE A4
DRN NJB	DATE 02/05/06	CHKD NBR	DATE 11/10/06	SCALE NTS	SHEET No. 1 OF 1