








37	69.32	63.50	54.71	49.68
25	53.03	47.04	38.25	33.12
15	39.14	33.32	24.54	19.18
09	30.81	24.99	16.21	10.96
SHELL	A	B	D	E



PCB DRILLING & RECOMMENDED PAD DETAILS
(AFTER PLATING - THICKNESS 1.60MM)


SECTION A - A




TRUE POSITIONING : $\phi 0.36$

ACCESSORIES DETAILS

RV VERSION



RX/RL VERSION



mat'l. code SEE TECH. SPEC				surface ISO 1302 ☒	tolerance ISO 406 ISO 1101	projection 	product family DELTA-D			
ltr	ecn no	dr	date	tolerances unless otherwise specified		MM	title DELTA-D A/S FEMALE PIP CONNECTOR US VERSION			
A	I07-0167	AS	2007-12-04	angles	linear					
B	I08-0175	AS	2009-01-14	0° $\pm 1^\circ$			dwg no C-DD-0099			
C	I09-0162	AS	2009-08-13							
				dr	ANISH.SALAM	2007-12-04	sheet 2 of 2 size A3			
				engr	ANISH.SALAM	2009-08-13				
				chr	ANISH.SALAM	2009-08-13	type Product Customer Drawing			
				appd	ANISH.SALAM	2009-08-13				
sheet index	revision sheet	C 1	C 2							