

12-Wire *euromast*® Cordsets, "C" Style Medium Plug Body

- Right Angle Male Connector
- NEMA 1, 3, 4, 6P and IEC IP 68 Protection
- 60 VAC/75 VDC, 2 A



Housing Style	Part Number	Cable	Features	Pinout	
WSC .. 1.736 [44.1] 1.377 [35.0] ø.531 [13.5] M12x1 WSCV ..** 1.736 [44.1] 1.377 [35.0] ø.591 [15.0] M12x1	WSC 12T-*	AWM PVC Grey 12x24 AWG 105°C 6.2 mm OD Cable #RF50991-*M†	<i>flexlife</i> ®	1. WH 2. BN 3. GN 4. YE 5. GY 6. PK 7. BU 8. RD 9. OG 10. TN 11. BK 12. VT	
	WSC 12T-*/S90	AWM PUR Grey 12x24 AWG 105°C 6.0 mm OD Cable #RF50990-*M†	<i>Cut/Abrasion Immune</i>		
	WSC 12T-*/S101	AWM TPE Black 12x24 AWG 105°C 7.0 mm OD Cable #RF50943-*M†	<i>flexLife-10, High Flex Over 10 Million Cycles</i>		
	WSC 12T-*/S618	AWM PVC Black 12x24 AWG Foil/Drain 105°C 7.0 mm OD Cable #RF50755-*M†	<i>RFI/EMI Shielding</i>		

* Length in meters. Standard cable lengths are 2, 4, 6, 8 and 10 meters. Consult factory for other lengths.
** Standard coupling nut material is nickel plated brass "WSC .."; "WSCV .." indicates 316 stainless steel.
† See Section N for *reelfast*® cable information.