

G83-6104/G83-6105



Models may vary from the image shown

Proven millions of times over!

There's a reason why this keyboard has been one of the most reliable and successful on the market for many years, with more than 30 million satisfied users.

Key benefits

- NTK technology (elastomer keys with membrane contact switches)
- Space-saving, compact design
- Long-lived and recycling-friendly
- Comfortable actuation
- Uniform switching characteristics
- Abrasion-proof inscription of key caps

Technical Data:

Layout (country or language):

Product dependant, see table "Models"

Housing colour:

Product dependant, see table "Models"

Key colour:

Product dependant, see table "Models"

Weight (product):

approx. 660 g

Total weight (with packaging):

approx. 1140 g

Cable Length:

approx. 1.75 m

Storage Temperature:

-20°C to 60°C

Operating Temperature:

0°C to 50°C

Current Consumption:

typ. 16 mA

Interface:

Product dependant, see table "Models"

Product approvals:

- cURus 
- VDE GS 
- c-tick 
- GOST-R 
- CE 
- FCC 

System requirements:

Product dependant, see table "Models"

Delivery Volume:

- G83-6104/G83-6105
- Printed instructions

Dimensions (product):

approx. 458 x 170 x 42 mm

Packaging dimensions:

approx. 493 x 210 x 47 mm

Keyboard:

- Key technology: NTK
- Service life, standard key: > 20 million key operations
- Operation characteristics: Soft pressure point
- Inscription technology: Laser
- Inscription layout: Normal
- Number of Keys: Product dependant, see table "Models"

Packaging Unit:

- Number of products in the master package: 65
- Number of master packages per pallet: 2

Warranty:

2 years

Errors, technical changes and delivery possibilities excepted.
Technical information refers only to the specifications of the products. Features may differ from the information provided.

Models:

(possible country/layout versions, others available on request)

	Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Interface	System requirements	Number of Keys
1	G83-6104	G83-6104LANUS-0	4025112012273	US English	light gray	light gray	DIN	DIN Interface	104
2	G83-6104	G83-6104LPNAR-0	4025112024863	English (US) / Arabic	light gray	light gray	PS/2	PS/2 connection	104
3	G83-6104	G83-6104LPNAR-2	4025112041754	English (US) / Arabic	black	black	PS/2	PS/2 connection	104
4	G83-6104	G83-6104LPNEU-2	4025112011887	US English with EURO symbol	black	black	PS/2	PS/2 connection	104
5	G83-6104	G83-6104LPNIL-0	4025112012174	English (US) / Hebrew	light gray	light gray	PS/2	PS/2 connection	104
6	G83-6104	G83-6104LPNJK-0	4025112054990	Japan (Katakana)	light gray	light gray	PS/2	PS/2 connection	104
7	G83-6104	G83-6104LPNRC-0	4025112055003	English (US) / Chinese	light gray	light gray	PS/2	PS/2 connection	104
8	G83-6104	G83-6104LRNEU-0	4025112010248	US English with EURO symbol	light gray	light gray	PS/2	PS/2 connection	104
9	G83-6104	G83-6104LRNRB-0	4025112044168	English (US) / Cyrillic	light gray	light gray	PS/2	PS/2 connection	104
10	G83-6104	G83-6104LUNEU-0	4025112010880	US English with EURO symbol	light gray	light gray	USB	USB connection	104
11	G83-6104	G83-6104LUNEU-2	4025112028793	US English with EURO symbol	black	black	USB	USB connection	104
12	G83-6104	G83-6104LUNIL-0	4025112056550	English (US) / Hebrew	light gray	light gray	USB	USB connection	104
13	G83-6104	G83-6104LUNRC-0	4025112049927	English (US) / Chinese	light gray	light gray	USB	USB connection	104
14	G83-6104	G83-6104LUNRG-0	4025112006876	US / Cyrillic	light gray	light gray	USB	USB connection	104
15	G83-6104	G83-6104LUNRG-2	4025112057915	US / Cyrillic	black	black	USB	USB connection	104
16	G83-6105	G83-6105LANBE-0	4025112010385	Belgium	light gray	light gray	DIN	DIN Interface	105
17	G83-6105	G83-6105LANCH-0	4025112046568	Switzerland	light gray	light gray	DIN	DIN Interface	105
18	G83-6105	G83-6105LANFR-0	4025112012280	France	light gray	light gray	DIN	DIN Interface	105
19	G83-6105	G83-6105LANGB-0	4025112021282	UK	light gray	light gray	DIN	DIN Interface	105

	Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Interface	System requirements	Number of Keys
20	G83-6105	G83-6105LANIT-0	4025112046551	Italy	light gray	light gray	DIN	DIN Interface	105
21	G83-6105	G83-6105LANPL-0	4025112039737	Poland	light gray	light gray	DIN	DIN Interface	105
22	G83-6105	G83-6105LANRD-0	4025112044670	Germany / Cyrillic	light gray	light gray	DIN	DIN Interface	105
23	G83-6105	G83-6105LANSL-0	4025112046544	Slovenia	light gray	light gray	DIN	DIN Interface	105
24	G83-6105	G83-6105LANTS-0	4025112046483	Czech Republic	light gray	light gray	DIN	DIN Interface	105
25	G83-6105	G83-6105LCPDE-0	4025112010255	Germany	light gray	light gray	DIN	DIN Interface	105
26	G83-6105	G83-6105LPNBE-0	4025112010262	Belgium	light gray	light gray	PS/2	PS/2 connection	105
27	G83-6105	G83-6105LPNEE-0	4025112044281	Estonia	light gray	light gray	PS/2	PS/2 connection	105
28	G83-6105	G83-6105LPNES-0	4025112010286	Spain	light gray	light gray	PS/2	PS/2 connection	105
29	G83-6105	G83-6105LPNES-2	4025112015236	Spain	black	black	PS/2	PS/2 connection	105
30	G83-6105	G83-6105LPNGB-0	4025112010699	UK	light gray	light gray	PS/2	PS/2 connection	105
31	G83-6105	G83-6105LPNGB-2	4025112034466	UK	black	black	PS/2	PS/2 connection	105
32	G83-6105	G83-6105LPNHU-0	4025112045646	Hungary	light gray	light gray	PS/2	PS/2 connection	105
33	G83-6105	G83-6105LPNNL-0	4025112010675	Netherlands	light gray	light gray	PS/2	PS/2 connection	105
34	G83-6105	G83-6105LPNNL-2	4025112050596	Netherlands	black	black	PS/2	PS/2 connection	105
35	G83-6105	G83-6105LPNNO-0	4025112040665	Norway	light gray	light gray	PS/2	PS/2 connection	105
36	G83-6105	G83-6105LPNNO-2	4025112027390	Norway	black	black	PS/2	PS/2 connection	105
37	G83-6105	G83-6105LPNPO-0	4025112010668	Portugal	light gray	light gray	PS/2	PS/2 connection	105
38	G83-6105	G83-6105LPNRD-0	4025112021220	Germany	light gray	light gray	PS/2	PS/2 connection	105
39	G83-6105	G83-6105LPNSF-2	4025112048524	Sweden / Finland	black	black	PS/2	PS/2 connection	105
40	G83-6105	G83-6105LRNBE-2	4025112017278	Belgium	black	black	PS/2	PS/2 connection	105
41	G83-6105	G83-6105LRNCH-0	4025112010644	Switzerland	light gray	light gray	PS/2	PS/2 connection	105
42	G83-6105	G83-6105LRNCH-2	4025112036965	Switzerland	black	black	PS/2	PS/2 connection	105
43	G83-6105	G83-6105LRNDE-0	4025112010002	Germany	light gray	light gray	PS/2	PS/2 connection	105
44	G83-6105	G83-6105LRNDE-2	4025112000034	Germany	black	black	PS/2	PS/2 connection	105
45	G83-6105	G83-6105LRNDK-0	4025112045837	Denmark	light gray	light gray	PS/2	PS/2 connection	105
46	G83-6105	G83-6105LRNDK-2	4025112047541	Denmark	black	black	PS/2	PS/2 connection	105
47	G83-6105	G83-6105LRNEE-2	4025112003080	Estonia	black	black	PS/2	PS/2 connection	105
48	G83-6105	G83-6105LRNFA-0	4025112053818	French / Arabic	light gray	light gray	PS/2	PS/2 connection	105
49	G83-6105	G83-6105LRNFR-0	4025112010309	France	light gray	light gray	PS/2	PS/2 connection	105
50	G83-6105	G83-6105LRNFR-2	4025112013638	France	black	black	PS/2	PS/2 connection	105
51	G83-6105	G83-6105LRNGR-0	4025112046476	Greece	light gray	light gray	PS/2	PS/2 connection	105

	Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Interface	System requirements	Number of Keys
52	G83-6105	G83-6105LRNHU-2	4025112003134	Hungary	black	black	PS/2	PS/2 connection	105
53	G83-6105	G83-6105LRNIT-0	4025112057441	Italy	light gray	light gray	PS/2	PS/2 connection	105
54	G83-6105	G83-6105LRNIT-2	4025112011405	Italy	black	black	PS/2	PS/2 connection	105
55	G83-6105	G83-6105LRNPL-0	4025112053825	Poland	light gray	light gray	PS/2	PS/2 connection	105
56	G83-6105	G83-6105LRNPL-2	4025112003318	Poland	black	black	PS/2	PS/2 connection	105
57	G83-6105	G83-6105LRNPO-2	4025112001178	Portugal	black	black	PS/2	PS/2 connection	105
58	G83-6105	G83-6105LRNRD-2	4025112049088	Germany / Cyrillic	black	black	PS/2	PS/2 connection	105
59	G83-6105	G83-6105LRNSF-0	4025112029516	Sweden / Finland	light gray	light gray	PS/2	PS/2 connection	105
60	G83-6105	G83-6105LRNSK-2	4025112003264	Slovakia	black	black	PS/2	PS/2 connection	105
61	G83-6105	G83-6105LRNSL-0	4025112010316	Slovenia	light gray	light gray	PS/2	PS/2 connection	105
62	G83-6105	G83-6105LRNSL-2	4025112011733	Slovenia	black	black	PS/2	PS/2 connection	105
63	G83-6105	G83-6105LRNTS-0	4025112023682	Czech Republic	light gray	light gray	PS/2	PS/2 connection	105
64	G83-6105	G83-6105LRNTS-2	4025112003219	Czech Republic	black	black	PS/2	PS/2 connection	105
65	G83-6105	G83-6105LUNBE-0	4025112010637	Belgium	light gray	light gray	USB	USB connection	105
66	G83-6105	G83-6105LUNBE-2	4025112043178	Belgium	black	black	USB	USB connection	105
67	G83-6105	G83-6105LUNCH-0	4025112017308	Switzerland	light gray	light gray	USB	USB connection	105
68	G83-6105	G83-6105LUNCH-2	4025112047350	Switzerland	black	black	USB	USB connection	105
69	G83-6105	G83-6105LUNDE-0	4025112010330	Germany	light gray	light gray	USB	USB connection	105
70	G83-6105	G83-6105LUNDE-2	4025112026027	Germany	black	black	USB	USB connection	105
71	G83-6105	G83-6105LUNDK-0	4025112010620	Denmark	light gray	light gray	USB	USB connection	105
72	G83-6105	G83-6105LUNDK-2	4025112047329	Denmark	black	black	USB	USB connection	105
73	G83-6105	G83-6105LUNES-0	4025112010613	Spain	light gray	light gray	USB	USB connection	105
74	G83-6105	G83-6105LUNES-2	4025112046216	Spain	black	black	USB	USB connection	105
75	G83-6105	G83-6105LUNFR-0	4025112010347	France	light gray	light gray	USB	USB connection	105
76	G83-6105	G83-6105LUNFR-2	4025112028779	France	black	black	USB	USB connection	105
77	G83-6105	G83-6105LUNGB-0	4025112010606	UK	light gray	light gray	USB	USB connection	105
78	G83-6105	G83-6105LUNGB-2	4025112047336	UK	black	black	USB	USB connection	105
79	G83-6105	G83-6105LUNGR-0	4025112056765	Greece	light gray	light gray	USB	USB connection	105
80	G83-6105	G83-6105LUNIT-0	4025112010590	Italy	light gray	light gray	USB	USB connection	105
81	G83-6105	G83-6105LUNIT-2	4025112046209	Italy	black	black	USB	USB connection	105
82	G83-6105	G83-6105LUNNL-0	4025112044717	Netherlands	light gray	light gray	USB	USB connection	105
83	G83-6105	G83-6105LUNNL-2	4025112050510	Netherlands	black	black	USB	USB connection	105

	Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Interface	System requirements	Number of Keys
84	G83-6105	G83-6105LUNNO-0	4025112013249	Norway	light gray	light gray	USB	USB connection	105
85	G83-6105	G83-6105LUNNO-2	4025112042843	Norway	black	black	USB	USB connection	105
86	G83-6105	G83-6105LUNPL-0	4025112052781	Poland	light gray	light gray	USB	USB connection	105
87	G83-6105	G83-6105LUNPO-0	4025112047398	Portugal	light gray	light gray	USB	USB connection	105
88	G83-6105	G83-6105LUNPO-2	4025112047343	Portugal	black	black	USB	USB connection	105
89	G83-6105	G83-6105LUNRD-0	4025112041990	Germany / Cyrillic	light gray	light gray	USB	USB connection	105
90	G83-6105	G83-6105LUNRD-2	4025112054082	Germany / Cyrillic	black	black	USB	USB connection	105
91	G83-6105	G83-6105LUNSF-0	4025112047381	Sweden / Finland	light gray	light gray	USB	USB connection	105
92	G83-6105	G83-6105LUNSF-2	4025112042621	Sweden / Finland	black	black	USB	USB connection	105
93	G83-6105	G83-6105LUNSL-0	4025112010583	Slovenia	light gray	light gray	USB	USB connection	105
94	G83-6105	G83-6105LUNTS-0	4025112022364	Czech Republic	light gray	light gray	USB	USB connection	105
95	G83-6105	G83-6105LUNTS-2	4025112040351	Czech Republic	black	black	USB	USB connection	105