

- ▼ Cable Ties
- [18-30 lb Tensile Strength](#)
- [40-50 lb Tensile Strength](#)
- [Heavy Duty Strength](#)
- [Heavy Duty Wide Strap](#)
- [Q Ties](#)
- [Releasable](#)
- [Releasable Heavy Duty](#)
- [Clamp Ties](#)
- [Double Head](#)
- [Identification](#)
- [Outside Serrated](#)
- [Stainless Steel - 304](#)
- [Stainless Steel - 316](#)
- [High Temp Applications](#)
- [Automatic Tool Cable Ties](#)
- [Swivel Clip Cable Tie](#)
- [Wire Harness Branch Ties](#)
- [Aerial Support Spacer Ties](#)
- [Releasable Grip Ties](#)
- ▶ Cable Ties with Fasteners
- ▶ Cable Tie Tools
- ▶ Clamps and Clips
- [Heatshrink Moulded Shapes](#)
- ▶ Mounts
- ▶ Heavy Duty Mounts
- ▶ Wire Connectors
- ▶ Wiring Duct
- ▶ Wiring Protection
- ▶ Labels, Printers and Software
- [Pre-Terminated Networking](#)
- ▶ Copper Network Solutions
- ▶ Fiber Network Solutions
- ▶ Jacks and Wall Plates
- ▶ Racks - Cable Management
- ▶ Surface Raceway Systems

T18R5C2

Standard Cable Tie, 4" Long, 18lb Tensile Strength, PA66, Green, 100/pkg

Article Number: 111-01853

Part Number: T18R5C2

Type: T18R



→ [Find a Distributor](#)

→ [Order Samples](#)


→ [Get Technical Drawings](#)

 |  [Share](#)

➔ Base Data

|                               |                                                                                                                                                                                                                                                                        |
|-------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Part No.                      | T18R5C2                                                                                                                                                                                                                                                                |
| Type                          | T18R                                                                                                                                                                                                                                                                   |
| Color                         | Green (GN)                                                                                                                                                                                                                                                             |
| Features                      | <ul style="list-style-type: none"><li>• Inside serrations allow for strong hold on cables and wire bundles.</li><li>• Head design provides high tensile strength with very low insertion force.</li><li>• Bent tail ensures a quick and simple installation.</li></ul> |
| Application Method            | Quick, simple application by hand or with HellermannTyton tensioning tools                                                                                                                                                                                             |
| Identification Plate Position | none                                                                                                                                                                                                                                                                   |
| Releasable Closure (Yes/No)   | No                                                                                                                                                                                                                                                                     |
| Tie Closure                   | plastic pawl                                                                                                                                                                                                                                                           |
| Typical Application           | Used to bundle and secure wire and cable.                                                                                                                                                                                                                              |
| Variant                       | Inside Serrated                                                                                                                                                                                                                                                        |

➔ Product Dimensions



|                       |                 |
|-----------------------|-----------------|
| Min. Tensile Strength | 18.0lbs / 80.0N |
| Length (L)            | 4.0" / 100.0mm  |
| Width (W) (imperial)  | 0.1"            |
| Width (W)             | 2.45mm          |
| Min. Ø Bundle         | 0.06" / 1.5mm   |
| Max. Ø Bundle         | 0.86" / 22.0mm  |

➔ Material and Specifications

|          |                      |
|----------|----------------------|
| Material | Polyamide 6.6 (PA66) |
|----------|----------------------|

|                               |                                                                                   |
|-------------------------------|-----------------------------------------------------------------------------------|
| US MILSPEC                    | MS3367-4-5                                                                        |
| CSA Certified                 | No                                                                                |
| Flammability                  | UL94 V2                                                                           |
| Material Specification        | RoHS / HF                                                                         |
| Operating Temperature         | -40 °F to +185 °F (-40 °C to +85 °C)                                              |
| ROHS Conformity               |  |
| Specification                 | MIL 53421 / UL ZODZ2.E64139                                                       |
| UL Listed (US and Canada)     | Yes                                                                               |
| UL Recognized (US and Canada) | Yes                                                                               |

 **Logistic and Packaging**

|                |               |
|----------------|---------------|
| Packaging Type | bag           |
| Pkg. Qty.      | 100           |
| Carton Qty.    | 10000         |
| EAN code       | 4031026423340 |
| UPC            | 089306069621  |

[Find a Distributor](#)

[Get Product Samples](#)

[Get Technical Drawings](#)