


Manual Switches

Rocker Switch Operators

AML54/56 Series

COLOR DISPLAY OPTIONS



Rocker operators are assembled to the switches by simply snapping them into recesses in the switch operator sockets.



Transmitted color — Color is displayed whether lamp is On or Off. Choice of 1-piece rockers (types 10 or 20) or rockers with clear cap and colored translucent insert (types 11 or 12).

Dead front hidden color/hidden legend — Rocker appears black with lamp Off. Legend and color appear when illuminated (types 30 or 40).

Projected color — Translucent white rocker with transparent colored insert (types 50 or 60). White rocker appears colored when illuminated.

AML54 ROCKER OPERATOR ORDER GUIDE (All possible color combinations may not be available.)

For AML14, AML24, AML34 incandescent or non-lighted display.

AML54-F	10	R	
Rocker Operator Type	Display/Legend Type	Rocker Color – See Note Below	
AML54-F	Transmitted Color	Full rocker, 1/2 rocker, or one side of two-piece rockers	Other side of two-piece rockers
 Full Rocker	10 No legend 20 With legend on cap	R Red Y Yellow G Green B Blue ***W White K* Black L* Gray A** Amber	R Red Y Yellow G Green B Blue ***W White K* Black L* Gray A** Amber
AML54-E	Transmitted Color		
 1/2 Rocker	(Clear cap and color insert) † 11 No legend 21 With legend on insert		
AML54-T	Dead Front †		
 Two-Piece Rocker	(Smoky gray cap and color insert) 30 No legend 40 With legend on insert		
	***Projected Color † (White cap and color insert) 50 No legend 60 With legend on cap		


NOTE: AML54-F10 and AML54-F20 are one-piece, one-color full rockers. Thus only one color code letter is necessary when ordering. Include a two letter code for all other AML54-E (and AML54-T) catalog listings.

*Not for lighted display.
**Not available with projected color or dead front.
***Insert is clear for projected color when "W" is used.
†Not available for use with AML34 power switches.

Example: **AML54-F10R**
Full rocker; with transmitted color, no legend; red.

AML56 ROCKER OPERATOR ORDER GUIDE

For AML36 neon display.

AML56-N	10	R	Y
Rocker Operator Type	Display/Legend Type	Lens Color	Rocker Color
AML56-N	Transmitted Color	T Clear R Red Y Yellow	R Red Y Yellow G Green B Blue W White K Black
 Full Rocker with Colored Lens	10 No Legend 20 With Legend		

AML56-N rockers have a colored lenticular lens window which extends over the neon lamp.

Example: **AML56-N10RY**
Full rocker; with transmitted color, no legend; yellow rocker and red lens.

Manuals



Manual Switches

Rocker Switch Operators

AML56 Series

AML56 ORDER GUIDE

For AML16 and AML26 LED display.

AML56-T	10	R	B
Rocker Operator Type	Display/Legend Type	Rocker Color – See Notes Below	
AML56-E  1/2-Rocker* (For one LED)	Transmitted Color 10 No Legend 20 With Legend	1/2-rocker or LED side of two-piece rockers	Other side of two piece rockers
AML56-T  Two-Piece Rocker (For one LED)		R Red Y Yellow G Green B Blue W White K Black L Gray	R Red Y Yellow G Green B Blue W White K Black L Gray
AML56-H  Two-Piece Rocker (For two LED's)			

Example: **AML56-T10RB**
Two-piece rocker; with LED window in one side, transmitted color, no legend; red (LED side) and blue (non-LED side).

HOW TO ORDER ROCKER LEGENDS

When specifying legended rockers, submit a legend order sheet to cover each catalog listing. These forms identify the maximum number of lines per area and the maximum characters per line, based on the type size you request. To insure proper legend orientation, rocker switch housings (when viewed from the panel front) should have the “MICRO SWITCH” identification facing UP or to the LEFT.

Rocker legend order sheets are shown on the following pages. Reproduce them on your office copier.

Legend Sheet	Form No.
AML54 Rockers	FO-63566
AML56 Rockers	FO-63564

* Notes:
¹ Only one color code letter is necessary for AML56-E 1/2-rockers. AML56-E, -T, and -H rockers have an open window which allows LEDs to be flush with the rocker surface.
² To order a 1/2-rocker without the LED “window,” specify an AML54-E listing from the previous page.

Page ___ of ___

Standard Legend Placement – 1. Transmitted Color—Legend on outer shell (Button
Use Special Legends Section *2. Dead Front—Legend on insert
for other placements. *3. Projected Color - Legend on outer shell (Button)
*4. Transmitted color with clear cap legend on insert.
*5. All legends will be centered within the legendable area.

EQ-8356A-F

Date)

Manuals

Modified Gothic lettering (A thru Z), numerals (0 thru 9) and Symbols below available in 5/64, 7/64, 9/64, 13/64 and 5/16.	A3 Modified Gothic									
STANDARD SYMBOLS AVAILABLE										
.	,	:	;	!	?	'	"	/	()	* &
\$	¢	#	%	o	+	-	±	÷	x	= ≠
→	↑	↓	↔	←	→	1/41/23/4	1/3 2/3	@	∞	

