





PART NR.	L1	L2	L3	
HM2H05PILF	3.0	13.45	11.15	AVAILABLE
HM2H05PI09LF	3.9	14.35	12.05	AVAILABLE
HM2H05PI15LF	4.5	14.95	12.65	AVAILABLE
HM2H05PI17LF	4.7	15.15	12.85	AVAILABLE
HM2H05PI19LF	4.9	15.35	13.05	AVAILABLE
HM2H05PI22LF	5.2	15.65	13.35	AVAILABLE
HM2H05PI30LF	6.0	16.45	14.15	AVAILABLE

- NOTES: 1. MEASURED AT THE BOTTOM
2. MATERIAL: GLASSREINFORCED POLYESTER UL94 - V0
3. THIS PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIONS AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
4. THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS.

rev	ecn no	dr	date
A	CONVERSION REVISION DS	KN	13-09-01
B	DG06-0536	KL	12-13-06
05	BEC 9. 3434	T.C	26-10-98
04	MARKING ADDED	M.F	22-09-98

FCI		www.fciconnect.com		✓	tolerance 1DEC ±0.2 1DEC 2DEC ±0.1 2DEC ANGLES ± 1° HOEKEN	projection 	MM 
Dr	W. P.	280294	Product family			size A4	Scale 1/3
Eng			Spec ref				
Chr			Material			ECN	
Appr							
 HM2 REAR HEADER WITH LOCKING DEVICE (125 POS)					dwg no BS, C , 201630, 018		Rev. B
catalog no		HM2H05PI--LF			CUSTOMER		sheet 1 of 1