

- Evaluate
 - FAQ's
- Design a Solution
 - Catalog Cut Sheet
 - PDFHST0.43-Q2Y
 - Part Drawings
 - PDFThick Wall P..
 - Specification Sheets
 - PDFThick Wall P..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

- Shrink ratio of 3:1 insulates a wide range of diameters and irregular shapes, which reduces inventory costs
 - Cross-linked, UV resistant material improves flame retardancy, chemical, and temperature resistance
 - Thick wall product seals and insulates in one step to speed installation
 - Meets Mil Spec AMS-DTL-23053/15 Class 1
- * For red, add 2 to end of part number package suffix (Example HST0.4 -3-Q2).

▪ Part Number	HST1.548-5-2Y
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Heat Shrink Thick Adhesive, 1.5"(38.1mm) Dia, Red
▪ Material	Highly flame retardant adhesive lined crosslinked polyolefin
▪ Color	Red
▪ CSA Certified	Yes
▪ Military Specification	AMS-DTL-23053/15 Class 1
▪ UL Listed	Yes
▪ UL Recognized	No
▪ Length (In.)	48.0
▪ Length (mm)	1219.2
▪ Copper Conductor Size Range	#3/0 – #400 MCM
▪ CE Compliant	No
▪ Conductor Size Range (mm)	95 – 185
▪ Flammability Rating	Flame Retardant
▪ Max. Connector O.D. (In.)	1.190
▪ Max. Connector O.D. (mm)	30.2
▪ Max. Recovered I.D. (In.)	0.50
▪ Max. Recovered I.D. (mm)	12.7
▪ Min. Cable O.D. (In.)	0.600
▪ Min. Cable O.D. (mm)	15.2
▪ Min. Expanded I.D. (In.)	1.50
▪ Min. Expanded I.D. (mm)	38.1
▪ Nominal Recovered Wall Thickness (In.)	0.16
▪ Nominal Recovered Wall Thickness (mm)	4.1
▪ Pricing Description	Heat Shrink Thick Adhesive, 1.5"(38.1mm) Dia, Red
▪ Shrink Ratio	3:1
▪ Temperature Range	-67°F – 230°F (-55°C – 110°C)
▪ Type	WET-SHRINK Thick Wall Heat Shrink Adhesive
▪ Min. Order UOM	PC
▪ Min. Order Qty.	5
▪ BOM Qty. (# of Pkgs.)	0
▪ Add to Favorite Product List	e

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.