




INSULATION

SERRATIONS

1

4.34 ±0.08 DIA

[.171 ±.003]

FOR #8 STUD

7.92

[.312]

6.35 MIN

[.250]

16.92 MAX

[.666]

20.96 MAX

[.825]

BODY

1

STAMP AMP 16-14* APPROX AS SHOWN

2

WIRE INSULATION DIA: 3.00-4.90 [.118-.193]

3

TONGUE MATERIAL THK: 0.79 ±0.05 [.031 ±.002]

4

MATERIAL: BODY - CU PER ASTM B152

SLEEVE - PVC, COLOR - BLUE

100	LOOSE PC,BOX	8-328527-1
5000	ON TAPE, REEL	2-328527-1
-	LOOSE PIECE	328527
QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED

CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL

PRODUCT INFORMATION OR

COPIES OF DRAWINGS

AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER

1-800-522-6752

FOR APPLICATION

TOOLING INFORMATION

TOOLING ASSISTANCE CENTER

1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING

TEMPERATURE:

105°C [221°F]

VOLTAGE RATING:

N/A

CIRCULAR MIL AREA:

1.04-2.62mm² [2,050-5,180]

SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM [INCHES]

MATERIAL

- 4

TOLERANCES UNLESS

OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.20[.008]

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

TIN PER ASTM B545

DWN

DK SCHRUM

08/06/92

CHK

RE HERSEY

11/10/92

APVD

M BARNABA

11/10/92

PRODUCT SPEC

108-1034

APPLICATION SPEC

NOT AVAILABLE

WEIGHT

-

CUSTOMER DRAWING

Tyco

Electronics

Tyco Electronics Corporation

Harrisburg, Pa 17105-3608

NAME

TERMINAL, RING TONGUE, PLASTI-GRIP

WIRE SIZE: 16-14 AWG

-

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-328527

RESTRICTED TO

-

SCALE

4:1

SHEET

1

OF

1

REV

H2

AMP 1470-19 REV 31MAR2000