





NOTE:
1. TEST:DC 300V/1s
2. INSULATION RESISTANCE:10m ohm
3. CONTACT RESISTANCE:2 ohm
4. PRODUCTS MEASURE UP TO THE ROHS
5. PVC TEGUMENT

10	PE BAG 6**9**0.04MM	IPCS
9	ELLIPTICAL CABLE TIE WITH CORE L=70MM	IPCS
8	TIN WIRE LEAD-FREE Ø0.6 ROHS	0.45g
7	P1&P2 PVC , BLACK 45P	16g
6	CONDUCTIVE COPPER PLATINUM P1.W:25MM*L:45MM1PCS ; P2.W:20MM*L:35MM1PCS	2PCS
5	GUMMED PAPER P1.W:20*L:50MM; P2.W:15*L:35MM	2PCS
4	PE1&P2 TRANSPARENT PE INTERNAL MODEL MATERIALS,LOW DENSITY	6g
3	HDMI C TYPE MALE: SHORT BODY PIN G/F,IRON SHELL-PLATED NICKEL,INSULATION BLACK	IPCS
2	HDMI A TYPE MALE: SHORT BODY PIN G/F,IRON SHELL-PLATED NICKEL,INSULATION BLACK	IPCS
1	UL20276[30AWG(7/0.10TS)*1P+EA+AL/MY]*4+30AWG(7/0.10TS)*1P+30AWG(7/0.10TS)*5C+AE8(16/6/0.12AM) OD:6.0mm PVC BLACK TEGUMENT CUT L=990±10mm(LS)	IPCS
No	DESCRIPTION	QTY



CnC Tech, LLC

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差參考表			TITLE: HDMI A/M TO CM CABLE PVC			
X.X	±0.38	X.X°	±3.00°	APPD:	PRODUCT NO: 742-10010-00300	
X.XX	±0.25	X.XX°	±2.00°	CHECK:	DATE	SCALE
X.XXX ±0.10	X.XXX° ±1.00°	DRAW:		2013.08.20	1:1	mm