




In-Line Phone Jacks

16PJ105, 16PJ119

KOBI CONN

In-Line Phone Jacks

16PJ105, 16PJ119



Dimensions: In.

SPECIFICATIONS	
Type:	mono, hi-rel, black plastic handle, in-line
Breakdown voltage:	500VAC for 1 minute
Insulation resistance:	100MΩ min. @ 500VDC
Contact resistance:	50mΩ max.
Life time:	5,000 cycles
Tolerance:	±.011

Mouser Stock No.	A	Size	
16PJ119	ø .141	3.5mm	
16PJ105	ø .102	2.5mm	
Number	Part Name		Remarks
1	Contact A	BSBM	Ni
2	Body	PA	
3	Contact B	PBS	Ni
4	Terminal	BSR	Ni
5	Cap	APS	

Date Last Revised: 4-5-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300425

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[16PJ119](#)