



Power Cord, C14 to BS1363 (UK), 0.6m
Part Number: AP9881



Output	
Maximum Total Current Draw per Phase	10A
Output Connections	(1) BS 1363
Input	
Input Connections	IEC-320 C14
Cord Length	0.61 meters
Number of Power Cords	1
Maximum Line Current per phase	10A
Physical	
Net Weight	0.36 KG
Shipping Weight	0.46 KG

Shipping Height	305.00 mm
Shipping Width	102.00 mm
Shipping Depth	102.00 mm
Color	Black

Conformance

Standard Warranty	2 years repair or replace
-------------------	---------------------------

Sustainable Offer Status

RoHS	Compliant
PEP	Available in Documentation tab
EOL	Available in Documentation tab

*,