

8-outlet, 8-ft cord, 2160 joule, RJ11 and coaxial protection - Protect It! Surge Suppressor

MODEL NUMBER: TLP808TELV



Description

Tripp Lite's TLP808TELV surge suppressor has 8 outlets, an 8-ft. cord with a space-saving right-angle plug, and diagnostic LEDs. The unit has a surge suppression rating of 2160 joules to handle the strongest surges.

Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. Built-in 2.2GHz gold coax jacks prevent surges from damaging your cable/satellite equipment. \$150,000 Ultimate Lifetime Insurance (USA & Canada only).

Features

- 8 outlets with integrated child safety covers; charcoal gray housing
- 8-ft. cord with space-saving right-angle plug
- Built-in RJ11 jacks (1 in/2 out) prevent surges from damaging your modem/fax/phone equipment; 6-ft. telephone cord included
- Built-in 2.2GHz gold coax jacks prevent surges from damaging your cable/satellite equipment; 6-ft. gold coax cable included
- Surge suppression rating: 2160 joules
- EMI/RFI noise filtering
- Can accommodate up to 3 transformers without blocking remaining outlets
- \$150,000 Ultimate Lifetime Insurance (USA and Canada Only)
- Diagnostic LEDs indicate protection present & ground present
- Audible alarm notifies user when the unit is damaged and needs to be replaced
- Keyhole supports for wall mounting
- Lighted power switch

Highlights

- 8 outlets / 8-ft. cord
- 2160 joule rating
- 2.2GHz gold coaxial surge protection
- Modem/fax surge protection
- \$150,000 Ultimate Lifetime Insurance (USA & Canada only)

Applications

- Ideal for home computers, TV/VCR/DVD players, stereos and other important electrical equipment

Package Includes

- TLP808TELV
- 6-ft. telephone cord
- 6-ft gold coax cable
- Instruction manual with warranty information

Specifications

OVERVIEW

Intended Application	Home/Office, Audio/Video
----------------------	--------------------------



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Circuit Breaker (amps)	15
Outlet quantity / type	8 NEMA 5-15R
Transformer accommodation	Supports 3 large transformer plug accessories without covering remaining outlets, accepts up to 6 transformers total
Outlet safety covers	Includes built-in sliding outlet safety covers
Outlet orientation	Single row of 5, plus a second row of 3 for transformer accommodation
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input plug features	Space-saving right angle input plug
Input cord length (ft.)	8
Input cord length (m)	2.44
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
Maximum Surge Amps	144000
LEDS ALARMS & SWITCHES	
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	2160
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150
UL1449 let through rating	330/400/400
EMI / RFI filtering	Up to 40 dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable (Coax) Protection Details	1 line
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (HWD/in)	11.41 x 8.66 x 2.04
Shipping Dimensions (HWD/cm)	28.98 x 22.00 x 5.18
Shipping weight (lbs)	2
Shipping weight (kg)	0.91
Unit Dimensions (HWD/in)	4.86 x 9.55 x 1.51
Unit Dimensions (HWD/cm)	12.34 x 24.26 x 3.84
Unit weight (lbs)	1.9
Unit weight (kg)	0.86
Material of construction	Plastic
Integrated keyhole mounting tabs	Keyhole mounting tabs enable wall mounting
Housing Color	Dark Gray
Receptacle Color	Dark Gray
AC line cord color	Dark Gray
Style	Strip
Outlets center to center measurement	Distance between standard outlets = 28.5mm; Distance between transformer outlets = 57mm
Keyhole slot center to center measurement	Distance between horizontal tabs = 75mm; Distance between vertical tabs = 41.6mm
SPECIAL FEATURES	
Additional Information	Pair of phone line output jacks serve as a line splitter to enable the protection of two devices sharing a single dialup phone line
Right-Angle Plug	Yes
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Industry Canada (Communications)	Industry Canada
Approvals	Exceeds IEEE 587 category A&B specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 Ultimate Lifetime Insurance

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP808TELT](#)[TV](#)