

JB hinge cover junction box



System accessories Page 531

Material:
Type 304 stainless steel
– Enclosure:
16 ga (1.5 mm)


Surface finish:
Enclosure and door:
#4 brushed

Protection rating:
UL/cUL Type 12
(IP 54 to EN 60 529/10.91)
UL/cUL Type 3R
UL/cUL 4X
(IP 66 to EN 60 529/10.91)
UL file #: E76083

Configuration:
– Door with 180° left-hand hinges
– Includes screwdriver insert and
wallmounting blind nuts

Detailed drawings:
Available at www.rittal-corp.com

**Note: zinc-plated enclosure
mounting panel sold separately
(see below)**



Depth: 3 - 4" (75 - 100 mm), Height: 4 - 8" (100 - 200 mm)

Height (H1) inches (mm)	PU	4 (100)	6 (150)	6 (150)	6 (150)	8 (200)	8 (200)	Page
Width (B1) inches (mm)		4 (100)	4 (100)	4 (100)	6 (150)	6 (150)	8 (200)	
Depth (T1) inches (mm)		3 (75)	3 (75)	4 (100)	4 (100)	4 (100)	4 (100)	
Panel Height inches (mm)		–	5 (135)	5 (135)	5 (135)	7 (185)	7 (185)	
Panel Width inches (mm)		–	3 (75)	3 (75)	5 (125)	5 (125)	7 (175)	
Part No.	1	JB040403H4	JB060403H4	JB060404H4	JB060604H4	JB080604H4	JB080804H4	
Weight lb (kg)		2 (0.9)	3 (1.4)	3 (1.4)	4 (1.6)	5 (2.0)	6 (2.5)	

Accessories

Mounting panel	1	–	JBMP0604	JBMP0606	JBMP0806	JBMP0808	633
Wallmount bracket Type 304	4						628

To order JB junction boxes in Type 316L stainless steel replace H4 ending with H6 (extended delivery times).

Depth: 4 - 6" (100 - 150 mm), Height: 8 - 12" (200 - 300 mm)

Height (H1) inches (mm)	PU	10 (250)	12 (300)	12 (300)	8 (200)	10 (250)	10 (250)	Page
Width (B1) inches (mm)		8 (200)	6 (150)	10 (250)	6 (150)	8 (200)	10 (250)	
Depth (T1) inches (mm)		4 (100)	4 (100)	5 (125)	6 (150)	6 (150)	6 (150)	
Panel Height inches (mm)		9 (235)	11 (285)	11 (285)	7 (185)	9 (235)	9 (235)	
Panel Width inches (mm)		7 (175)	5 (125)	9 (225)	5 (125)	7 (175)	9 (225)	
Part No.	1	JB100804H4	JB120604H4	JB121005H4	JB080606H4	JB100806H4	JB101006H4	
Weight lb (kg)		8 (3.4)	6 (2.7)	9 (4.1)	6 (2.5)	8 (3.4)	9 (3.9)	

Accessories

Mounting panel	1	JBMP1008	JBMP1206	JBMP1210	JBMP0806	JBMP1008	JBMP1010	633
Wallmount bracket Type 304	4							628

To order JB junction boxes in Type 316L stainless steel replace H4 ending with H6 (extended delivery times).

JB hinge cover junction box

Depth: 6 - 10" (150 - 250 mm), Height: 12 - 16" (300 - 400 mm)

Height (H1) inches (mm)	PU	12 (300)	12 (300)	14 (350)	16 (400)	12 (300)	16 (400)	16 (400)	Page
Width (B1) inches (mm)		10 (250)	12 (300)	12 (300)	14 (350)	10 (250)	14 (350)	14 (350)	
Depth (T1) inches (mm)		6 (150)	6 (150)	6 (150)	6 (150)	8 (200)	8 (200)	10 (250)	
Panel Height (G1) inches (mm)		11 (285)	11 (285)	13 (335)	15 (385)	11 (285)	15 (385)	15 (385)	
Panel Width (F1) inches (mm)		9 (225)	11 (275)	11 (275)	13 (325)	9 (225)	13 (325)	13 (325)	
Part No.	1	JB121006H4	JB121206H4	JB141206H4	JB161406H4	JB121008H4	JB161408H4	JB161410H4	
Weight lb (kg)		10 (4.5)	11 (5.0)	12 (5.5)	15 (6.8)	11 (5.0)	17 (7.7)	19 (8.6)	
Accessories									
Mounting panel	1	JBMP1210	JBMP1212	JBMP1412	JBMP1614	JBMP1210	JBMP1614		633
Wallmount bracket Type 304	4	1594.000							628

Note: To order JB junction boxes in Type 316L stainless steel replace H4 ending with H6 (extended delivery times).



Rittal Israel

RITTAL Enclosure Systems Ltd.
 13, Hatarshish St. Zone 29 • P.O. Box 3597
 Industrial Park, Caesarea 38900
 Phone: +972 (0) 4 6275 505
 Fax: +972 (0) 4 6275 535
 E-mail: moshe@rittal.co.il
www.rittal.co.il