

Search within category

GO

BUY NOW

DESIGN / INSTALL



UTPCH4MRDY

Category 5e, UTP patch cord with Pan-Plug™ Modular Plugs on each end. Red, 4 meters.
UTPCH4MRDY replaces UTPCH4MRD

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
Note	UTPCH4MRDY replaces UTPCH4MRD			
Performance Level	Category 5e			
Cable Type	U/UTP			
Cable Color	Red			
Length (ft.)	13.12			
Length (m)	4.0			
Flammability Rating	CM			
Termination End 1	Modular Plug			
Termination End 2	Modular Plug			
Standards	ANSI/TIA-568-C.2, ISO 11801 Class EA, IEEE 802.3af, 802.3at, 802.3bt type 3 and type 4, UL 1863.			
CE Compliant	Yes			
Nominal Cable O.D. (In.)	0.22			
Nominal Cable O.D. (mm)	5.5			
Operating Temperature	14°F to 140°F (-10°C to 60°C)			
Storage Temperature	-40°F to 158°F (-40°C to 70°C)			
UL5A Listed	No			
AWG Size	24			
BMEcat - Type of Connector	RJ45 8(8)			
Boot Color	No Boot			
Conductor Material	Copper			
Installation Temperature	-40°F to 158°F (-40°C to 70°C)			
Part Features	100% performance tested for wire map, NEXT and return loss, Centered de-embedded plug, Integral pair manager, Patented tangle-free latch			
RoHS Compliancy Status	Compliant			
Min. Order Qty.	1			