




LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	APVD
			F4	REVISED PER ECR-12-003652	24FEB12	JR GP




- 1
- PRODUCT PROVIDED IN STRIP FORM ON REELS; BREAKS MAY BE PRESENT.
- 2
- DIMENSIONS IN BRACKETS ARE IN INCHES.
- 3
- CRIMP WIDTH: .180 F
CRIMP HEIGHT (±.002)=(TOTAL CMA+23,000)/312,500
CRIMP WIDTH: .220 F
CRIMP HEIGHT (±.002)=(TOTAL CMA+25,000)/375,000
GENERAL APPLICATION GUIDELINES MUST BE FOLLOWED AS SPECIFIED IN CATALOG #82221
FOR APPLICATOR INFORMATION CALL : 1-800-722-1111
FOR PRODUCT INFORMATION CALL : 1-800-522-6752
- 4
- WIRE RANGE 7000-14000 CMA



SECTION A-A
SCALE : 10:1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 31JAN06		 TE Connectivity							
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME							
		0 PLC ± -		SPLICE, AMPLIVAR 7000-14000 CMA -							
		1 PLC ± -									
		2 PLC ± 0.38[.015]									
		3 PLC ± -									
4 PLC ± -		PRODUCT SPEC		SIZECAGE CODEDRAWING NORESTRICTED TO							
ANGLES ± 1°		-									
MATERIAL REF 0.64±0.03 [.025±.001] BRASS		FINISH TIN PL.		APPLICATION SPEC 114-2003		A300779C-62310		-			
				WEIGHT -		CUSTOMER DRAWING					
						SCALE 5:1		SHEET 1 OF 1		REV F4	