




Rating	21A 14VDC	<div>Mounting Hole</div> <div></div> <table><tr><td>Thickness</td><td>X</td><td>Y</td></tr><tr><td>0.75~1.25</td><td>21.2±0.1</td><td>36.6±0.1</td></tr><tr><td>1.25~2</td><td>21.2±0.1</td><td>36.8±0.1</td></tr><tr><td>2~3</td><td>21.2±0.1</td><td>37.0±0.1</td></tr></table>	Thickness	X	Y	0.75~1.25	21.2±0.1	36.6±0.1	1.25~2	21.2±0.1	36.8±0.1	2~3	21.2±0.1	37.0±0.1	<div>Circuit Diagram</div> <div></div>
Thickness	X		Y												
0.75~1.25	21.2±0.1		36.6±0.1												
1.25~2	21.2±0.1		36.8±0.1												
2~3	21.2±0.1		37.0±0.1												
Contact Resistance	50m ohm Max.														
Insulation Resistance	DC 500V 100M ohm Min.														
Dielectric Strength	AC 1500V 1 minute														
Switch Function	4P SPDT ON-OFF-ON														
Operation Temperature	-20°C~85°C														



Material:

Frame: Black, Nylon#66




Actuator: Black, Nylon#66

LED 1: Green

LED 2: Red

Printed: None

Water proof and dust proof to fit IP-56



RoHS Compliant

1 SPDT Was SPST & Removed AC Ratings & added DC Ratings. 8/17/10

**CW INDUSTRIES**  
Southampton, Pa. 18966  
Tel 215.355.7080/www.cwind.com

Date Drawn: 5/18/10

Rev. 1

Unit: mm

Checked By: G. Guld

Title: **ROCKER SWITCH**

CW P/N: **GRB263D2BBGR2D1**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CW Industries:](#)

[GRB263D2BBGR2D1](#)