

## Power Supply Cord with Shako Power (Mains) Plug, Angled



CEE 7 / VII

CEE 7 / VII / DIN  
49441-R2

## Description

- Power Supply Cord, Protection class I, Pin temperature 70 °C,
- Cable

## Approvals

- VDE Certificate Number: 40005911


## Weblinks

[pdf](#), [html](#), [General Product Information](#), [Approvals](#), [RoHS](#), [CHINA-RoHS](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Accessories](#), [Detailed request for product](#)

## Technical Data

|                           |                                                                   |
|---------------------------|-------------------------------------------------------------------|
| Ratings IEC               | 16 A / 250 VAC; 50 Hz                                             |
| Ratings UL/CSA            | 16 A / 250 VAC; 60 Hz                                             |
| Dielectric Strength       | > 4 kVDC between L-N<br>> 2 kVAC between L/N-PE<br>(1 min/50 Hz)  |
| Allowable Operation Temp. | -25 °C to 70 °C                                                   |
| Degree of Protection      | from front side IP 20 acc. to IEC 60529                           |
| Protection Class          | Suitable for appliances with protection class 1 acc. to IEC 61140 |
| Terminal                  | moulded Ground terminal                                           |
| Material: Housing         | PVC, black or grey                                                |

## Dimensions



## Config. Code

## 422u - R - Type - D - Length

The characters are placeholders for the correspondingly keys of selections from the key tables.  
Typ steht für die Dose bzw. 2. Seite, Länge ist die Leitungslänge in mm.

422u - **R** - Type - D - Length = cord type

| cord type                                                      | Configuration key |
|----------------------------------------------------------------|-------------------|
| H05VV-F 3G1,0mm2                                               | I                 |
| H05VV-F 3G1,5mm2                                               | K                 |
| Cord definition is detailed in general product information XXX |                   |

422u - R - **Type** - D - Length = Cord end 2

| Cord end 2                                                       |
|------------------------------------------------------------------|
| zzzz, 1654, 2512, 2530, 3012, 3013, 3020, 3027, 3030, 311L, 312L |

422u - R - Type - **D** - Length = Color

| Color         | Configuration key |
|---------------|-------------------|
| Black         | A                 |
| Grey          | B                 |
| grey: RAL7032 | E                 |

422u - R - Type - D - **Length** = Cord length

| Cord length                                                  |
|--------------------------------------------------------------|
| zzzz, 000500, 001000, 001500, 002000, 002500, 003000, 005000 |

Cord length in mm

|                       |         |
|-----------------------|---------|
| <b>Packaging unit</b> | 100 Pcs |
|-----------------------|---------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schurter:

[6051.0021](#) [6051.0025](#) [6051.0027](#) [6051.0028](#) [6051.003](#) [6051.0030](#)