

リバーシブル キースイッチ

KEYSWITCHES




S-19
亜鉛合金製

特 徴 Feature

- リバーシブルキー採用
- 防塵シャッター付
- Reversible key
- Lock has dustproof shutter

- 仕 様
- 製品質量: 55g
 - 材 質: 本体・キー・シリンダー錠部/亜鉛合金 (ZDC) (本体・ステンレスカバー付)
 - 表面仕上: 本体・シリンダー錠部/亜鉛めっきクロメート処理 (MZZn-C) キー/ニッケルめっき (MZNi)
 - 鍵 番 号: R0220
 - 同一鍵番号・鍵違いがあります。
 - 付 属 品: キー2本
 - コンピュータ周辺機器・各種電源スイッチ
 - 標準在庫品
 - 定 格: AC125V・3A (抵抗負荷) DC30V・3A (抵抗負荷)
 - 最小適用負荷: DC5V・100mA (抵抗負荷)
 - 接触抵抗: 20mΩ以下 (初期値)
 - 絶縁抵抗: 100MΩ以上 (500VDC)
 - 耐 電 圧: (50/60Hz, 1分間) 非連続端子間 AC1000V 各端子と非充電金属部間 AC1500V
 - 耐 久 性: 機械的3万回以上 電氣的1.5万回以上
 - 接点材料: 銀めっき
 - 使用周囲温度: -20~+70℃ (氷結なきこと)
 - 使用周囲湿度: 85%RH以下 (結露なきこと)
 - 耐 振 動: 10~55Hz 複振幅1.5mm
 - 耐 衝 撃: 30G以上
 - 微小負荷タイプはお問合せください。
- 用 途
納 期
ス イ ッ チ 部
特 性


- 備 考
- Specifications
- Mass: 55g
 - Material: Main body, cylinder and lock: Zinc alloy (ZDC) (Main body with stainless steel cover)
 - Finish: Main body and lock: Zinc plating chromate treatment (MZZn-C) Key: Nickel plating (MZNi)
 - Key No.: R0220
 - Keyed alike and key differences are available.
 - Accessories: Two keys
 - Computer peripherals and various power switches
 - Rated: AC125V 3A (resistance load) DC30V 3A (resistance load) Min. applicable load: DC5V 100mA (resistance load)
 - Contact resistance: 20mΩ or less
 - Insulation resistance: 100MΩ or more (500VDC)
 - Withstand voltage: (50/60 Hz, one minute) Between non-continuous terminals: AC1000V Between each terminal and non-charged metal: AC1500V
 - Durability: Mechanical: 30,000 time or more Electrical: 15,000 time or more
 - Contact material: Silver plating
 - Ambient temperature: -20℃ to +70℃ (non-freezing)
 - Operating humidity range: 85%RH or less (non-condensing)
 - Vibration resistance: 10 to 55Hz multiple-amplitude 1.5mm
 - Impact resistance: 30G or more





S-19-90-E-1



キーNo. R0220
Key



パネル穴明け寸法
Panel drilling dimensions



(2回路2接点型の裏面)
(Back of two-circuit-two-contact type)

商品番号 Product No.	RoHS 10/27	CAD	コード Code	単 価 Price	量販価格 数量 Quantity	Bulk Price 単価 Price
S-19-90-E-1同番 Keyed alike	●	2D	40211	¥1,600	10個~	¥1,536
S-19-90-E-1鍵違い Key differences		2D	40212	¥1,950	10個~	¥1,872
S-19-90-E-2同番 Keyed alike		2D	40215	¥1,650	10個~	¥1,584
S-19-90-EF-1同番 Keyed alike		2D	40213	¥1,550	10個~	¥1,488
S-19-90-EF-1鍵違い Key differences		2D	40214	¥1,900	10個~	¥1,824
S-19-90-EF-2同番 Keyed alike		2D	40217	¥1,600	10個~	¥1,536


●: RoHS10指令対応品 ▲: RoHS10指令に対応可能です。 ※大量のご注文は更にお安くなります。

接点構成表


Contact structures table

●印の位置は鍵が抜き差しできます。
Position of mark (●) shows that key can be inserted/removed.

商品番号 Product No.	鍵回転角度 Key turning angle	E 位置 E position	F 位置 F position
S-19-90-E-1 (1回路2接点型) (one-circuit-two-contact type)			
S-19-90-EF-1 (1回路2接点型) (one-circuit-two-contact type)			
S-19-90-E-2 (2回路2接点型) (two-circuit-two-contact type)			
S-19-90-EF-2 (2回路2接点型) (two-circuit-two-contact type)			



Specific use
Switch
character-
istic



1本のキーでキュービクル・コインロック・キースイッチの扉の管理ができます。
A single key can control all doors of cubicle, coin lock and keyswitch.



S

CONTROL KEYSWITCHES
コントロール
キースイッチ

ソレノイド付
キースイッチ

オペレーター
キースイッチ

止め金付
キースイッチ

マイクロ
スイッチ