



Sample photo

Order symbol: CAB ABS 403018 T
Product nbr: 8183050
Description: Cabinet, ABS
Remarks: Latches on the long side, smooth

EAN: 6418074020277
El. number:
 Finland 3424364
 Denmark 8212020553
 Italy 7812040
 Sweden 2540041

Including: Cabinet base, door with EPDM gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:			
L	W	H	
mm:	400	300	180
inch:	15.7	11.8	7.1
Materials:			
Material:	ABS		
Base colour:	RAL 7035		
Cover colour:	Smoked grey		
Gasket material:	EPDM		
Temperatures:			
Short term:	-40 ... 80 °C		
Continuous:	-40 ... 60 °C		
Short term:	-40 ... 175 °F		
Continuous:	-40 ... 140 °F		
Accessories:			
EKIV 43	Mounting plate		
EKIV 27	DIN-35 Mounting rail		
EKIV 37	DIN-35 Mounting rail		
FP A 43	Swing-out door, aluminium		
FP 43	Front plate		
FP 12x2-43	Front Plate		
FP 12x3-43	Front Plate		
DRF 43/44	DIN rail frame set		

Rating:	
Ingress Protection (EN 60529):	IP 65
Impact Resistance (EN 50102):	IK 08
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	Yes
Flammability Rating (UL 746 C 5):	UL 94 HB
Glow Wire Test (IEC 695-2-1) °C:	650
NEMA Class:	NEMA 1, 4, 4X, 12, 13
Certificates:	
Fimko	
Europe EN 50298 1998	
Gost R	

