

- ☐ Cable Ties

☐ Cable Ties with Fasteners

☐ Cable Tie Tools

☐ Clamps and Clips

☐ Mounts

☐ Heavy Duty Mounts

☐ Wiring Duct

☐ Solid Wall

☒ Slotted Wall

☐ High Density Slotted Wall

☐ Covers

☐ Accessories

☐ Wiring Protection

☐ Labels, Printers and Software

☐ Pre - Terminated Networking

☐ Copper Network Solutions

☐ Fiber Network Solutions

☐ Jacks and Wall Plates

☐ Residential Solutions

☐ Racks - Cable Management

☐ Surface Raceway Systems

SL1X4G4

Slotted Wall Duet1" X 4" NonAdhesive, PVC, Gray, 120' / carton

Article Number: 181 - 14003
Part Number: SL1X4G4
Type: SL1X4
Material: PVC




[Find a Distributor](#)
[Order Samples](#)
[Get Technical Drawings](#)

1. Base Data

Part No.	SL1X4G4
Type	SL1X4
Color	Gray
Features	Slotted wall duct features break -away fingers which provide additional access for wire leads. Slotted wall duct is manufactured with two score lines. The first score line is at the base of the finger, allowing the finger to be bent and broken away when a greater opening is required. The second score line is lower allowing a section of the sidewall to be easily removed by cutting the sidewall down to the lower score line. Use HellermannTytonâ€™s TDNT notching tool and snap out the desired section. Both score lines provide smooth edges to ensure worker safety. Strong fingers prevent unwanted breaking. The fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct. Restricted opening design in the finger of the duct helps keep wires in place. Restriction also prevents unintended removal of wires and permits any individual wire to be traced without disconnection.

2. Product Dimensions



Length (L)	6 ft / 1.83 m
Width (W)	1.00 " / 25.40 mm
Width (W2)	1.00 " / 25.40 mm
Width (W3)	10.16 mm
Width (W4)	1.00 " / 25.40 mm
Width (W5)	3.6 " / 91.4 mm
Height (H)	4.06 " / 103.12 mm
Mounting Hole Centers	4.00 " / 101.60 mm

4. Material and Specifications

Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Certification	CSA / UL
CSA Certified	Yes
Flammability	self -extinguishing
Material Specification	RoHS
Operating Temperature	+122 Â°F (+50 Â°C)

Logistic and Packaging

Packaging Type	carton
Pkg. Qty.	120 ft / 36.6 m
Carton Qty.	120
UPC	089306304524

Miscellaneous

UL Recognized (US and Canada)	Yes
Width (W3)	.40 "

Find a Distributor

Get Product Samples

Get Technical Drawings

Customers Who Bought This Item Also Bought

	Wiring Duct Cover Width 1.00" PVC, Gray, 120' / Pkg. Qty. Part No: TC1G4 Article No: 181 - 91004
	Slotted Wall Duct - 2" X 4" Non -Adhesive, PVC, Gray, 120' / carton Part No: SL2X4G4 Article No: 181 - 24008
	Wiring Duct Cover Width 2.00" PVC, Gray, 120' / Pkg. Qty. Part No: TC2G4 Article No: 181 - 92005
	Cable Tie, 30lb. 5.9", Max Bun Dia. 1.38" PA66 Natural, 1000/Pk Part No: T30R9M4 Article No: 111 - 03047
	Wiring Duct Cover Width 1.50" PVC, Gray, 120' / Pkg. Qty. Part No: TC1.5G4 Article No: 181 - 91507

This product was found in [Wiring Duct](#) > [Slotted Wall](#)