



Add to BOM | Add to Favorites

Braided Expandable Sleeving provides continuous abrasion resistance for wires, cables and tubing. The highly flexible open weave will not trap heat or humidity.

Product Details Related Documents

Std. Pkg. Qty.	1
Std. Ctn. Weight (lb)	0.0000
Std. Ctn. Volume (cf)	0.0000
Std. Pallet Weight (lb)	20.0000
Std. Pallet Volume (cf)	0.000000
RoHS Compliancy Status	Compliant
Part Description	Braided Expandable Sleeving provides continuous abrasion resistance for wires, cables and tubing. The highly flexible open weave will not trap heat or humidity.
Product Type	Braided Expandable Sleeving
Material	Polyethylene Terephthalate
Color	Black
CSA Certified	Yes
UL Recognized	E116868
Length (m)	61.0
CE Compliant	No
Temperature Range	-94°F - 257°F (-70°C - 125°C)
Nominal I.D. (mm)	50.80
Nominal I.D. (In.)	2.00
Nominal Diameter Range (mm)	38.1 - 88.9
Nominal Diameter Range (In.)	1.50 - 3.50
Flammability Rating	HB
Type	Braided Expandable Sleeving
Pricing Description	SLEEVING-EXPLANDABLE 2" DIA, 200FT REEL
Length Per Reel (ft.)	200
Length Per Reel (m)	61.0
Min. Order Qty.	1.0000

