



Wert fehlt!

Order number	6SE6400-3CC00-2AD3
Number of phases / of input voltage	3
Type of / input voltage	AC
Input voltage	380 ... 480
Output current / rated value	1.9 A
Effective power loss	
• at 50 Hz	6 W
• at 60 Hz	7 W
• Design of electrical connection / for mains supply line	Screw-type terminals
• Design of the electrical connection / for motor outgoing line	Cable
Type of connectable conductor cross-sections / for load-side outgoing feeder	3 x AWG16
Connectable conductor cross-section	
• for line supply conductor	6 mm ²
• for load-side outgoing feeder	1.5 mm ²

Cable length / of connecting cable / for load-side outgoing feeder	0.38 m
Design of electrical connection / for PE conductor	M5 stud bolt
Protection class IP	IP20
Width	75.5 mm
Height	201 mm
Depth	50 mm
Net weight	1.3 kg
Verification of suitability	cURus

Further information

Information und Download Center

https://www.automation.siemens.com/mcms/infocenter/content/en/Pages/order_form.aspx

Technical documentation

<http://w3.siemens.com/mcms/mc-solutions/en/motion-control/support/technical-documentation/Pages/technical-documentation.aspx>

Industry Mall

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/6SE64003CC002AD3/all>

Industry Online Support

<http://support.automation.siemens.com/WW/view/en/6SE64003CC002AD3/all>