

SEMELAB

SEMELAB LTD T-22-01

BI-POLAR TRANSISTORS (CECC AND HIGH REL) & HIGH ENERGY

Type Number	Rel Code	Pol	Package	Vceo	Ic (cont)	Hfe	@ Vce/Ic	FT	Pd
BYV32-150M-ISO	HR	DIODE	TO220M	150					
BYV32-200M-ISO	HR	DIODE	TO220M	200					
BYV32-200RM-ISO	HR	DIODE	TO220M	200					
BYV32-50M-ISO	HR	DIODE	TO220M	50					
BYV34-300M-ISO	HR	DIODE	TO220M	300					
BYV34-400M-ISO	HR	DIODE	TO220M	400					
BYV34-500M-ISO	HR	DIODE	TO220M	500					
BYW29-100M-ISO	HR	DIODE	TO220M	100					
BYW29-150M-ISO	HR	DIODE	TO220M	150					
BYW29-200M-ISO	HR	DIODE	TO220M	200					
BYW29-50M-ISO	HR	DIODE	TO220M	50					
CV9936	CECC								
MJ11028	HR	NPN	TO3	60	50	1K-18K	5/25		300
MJ11029	HR	PNP	TO3	60	50	1K-18K	5/25		300
MJ11030	HR	NPN	TO3	90	50	1K-18K	5/25		300
MJ11031	HR	PNP	TO3	90	50	1K-18K	5/25		300
MJ11032	HR	NPN	TO3	120	50	1K-18K	5/25		300
MJ11033	HR	PNP	TO3	120	50	1K-18K	5/25		300
MJ14000	HR	NPN	TO3	60	70	15-100	3/50		300
MJ14001	REQ	PNP	TO3	60	70	15-100	3/50		300
MJ14002	HR	NPN	TO3	80	70	15-100	3/50		300
MJ14003	HR	PNP	TO3	80	70	15-100	3/50		300
MJ15001	HR	NPN	TO3	140	15	25-150	2/4	2M	200
MJ15002	HR	PNP	TO3	140	15	25-150	2/4	2M	200
MJ15003	HR	NPN	TO3	140	20	25-150	2/5	2M	250
MJ15004	HR	PNP	TO3	140	20	25-150	2/5	2M	250
MJ15011	HR	NPN	TO3	250	10	25-100	2/2		200
MJ15012	HR	PNP	TO3	250	10	20-100	2/2		200
MJ15015	HR	NPN	TO3	120	15	20-70	4/4		180
MJ15016	HR	PNP	TO3	120	15	20-70	4/4		180
MJ15022	HR	NPN	TO3	200	16	15-60	4/8	4M	250
MJ15023	HR	PNP	TO3	200	16	15-60	4/8	4M	250
MJ15024	HR	NPN	TO3	250	16	15-60	4/8	4M	250
MJ15025	HR	PNP	TO3	250	16	15-60	4/8	4M	250
MJ16010	HR	NPN	TO3	450	15	5min	5/15		175
MJ16012	HR	NPN	TO3	450	15	7min	5/15		175
MJ2500	HR	PNP	TO3	60	10	1kmin	3/5	1M	150
MJ2501	HR	PNP	TO3	80	10	1kmin	3/5	1M	150
MJ2955	CECC	PNP	TO3	60	15	20-70	4/4	2.5M	115
MJ3000	HR	NPN	TO3	60	10	1kmin	3/5	1M	150
MJ3001	HR	NPN	TO3	80	10	1kmin	3/5	1M	150
MJ3201	HR	NPN	TO66	225	0.1	30-200	10/50m	15M	15
MJ3202	HR	NPN	TO66	300	0.1	30-200	10/50m	15M	15
MJ3238	HR	PNP	TO66	150	8	2min	2/4	20M	75
MJ4032	HR	NPN	TO66	300	0.1	30-200	10/50m	15M	15
MJ4035	HR	NPN	TO3	100	16	1kmin	3/10		150
MJ4400	HR	NPN	TO66	300	5	12-60	2/1.5	20M	100
MJ4401	HR	NPN	TO66	400	5	12-60	2/1.5	20M	100
MJ4502	REQ	NPN	TO3	100	30	25-100	2/7.5	2M	200
MJ4646	REQ	PNP	TO39	300	0.5	25min	10/0.1	40M	5
MJ6502	REQ	PNP	TO3	250	8	15min	5/2		125
MJ6503	REQ	PNP	TO3	400	8	15min	5/2		125
MJ802	REQ	NPN	TO3	100	30	25-100	2/7.5	2M	200
MJ8100	REQ	PNP	TO39	60	5	25-180	2/2	30M	10
MJ8101	REQ	PNP	TO39	80	5	25-180	2/2	30M	10
PO27	REQ		TO39						
PO38	REQ	PNP	TO39	300	0.5	25-200	0.5/20u	35M	0.6