


P1:	M-942C
P2:	M-Y928A
	M-928A



NOTE: All relevant materials are complied with RoHS directive .

P1		P2	
1	—	1	RED 24#
2	—	2	WHITE
3	—	3	GREEN
4	—	4	BLACK 24#
SHIELD	—	SHIELD	

5	BLACK HEAT SHIRK TUBE $\phi 1.0 \times 10 \text{mm}$	1	M519
	MOLDED PE COLOR TRANSPARENT		TWN
	MOLDED PVC BEIGE		M304
4	MOLDED PVC BEIGE		M304
3	USB 2.0 CABLE, UL STYLE 1 TWISD PAIR 28AWG AND 2C 24AWG, OD 4.7mm, JACKET BEIGE, DRAWING No. EUAB2801P2402C-015	L-20mm	M304
2	USB A FEMALE 2.0, GOLD PLATING 30u" ON CONTACTS, WHITE INSULATOR	1set	M108
1	USB A MALE 2.0, GOLD PLATING 30u" ON CONTACTS, WHITE INSULATOR, SHORT TYPE	1set	M108
No.	DESCRIPTION	Q'TY	Supplier

USB2-022

Cable Length Unless Other Spec.	
Tolerances:	
0 ~200mm	$\pm 10 \text{mm}$
201~1000mm	$\pm 20 \text{mm}$
1001 ~1500mm	$\pm 25 \text{mm}$
1501~2100mm	$\pm 30 \text{mm}$
2100mm↑	$\pm 40 \text{mm}$

UNIT:mm



CHECKED