

SAIL-M12BG-CD-5.0A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



The most reliable way of achieving connections between two I/O slaves or between the control and one I/O subscriber is by way of pre-assembled cables. The line of cables covers PROFIBUS, CANopen, DeviceNet™, EtherCAT and Ethernet.

General ordering data

Order No.	1964690500
Type	SAIL-M12BG-CD-5.0A
Version	Bus line, Socket, jumpered: No, No. of poles: 5, 5 m, PUR/ TPE
GTIN (EAN)	4032248650125
Qty.	1 pc(s).

SAIL-M12BG-CD-5.0A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com

Technical data**Dimensions**

Net weight	292 g
------------	-------

General data

Bus line connection via	screw terminals M12	Cable diameter, max.	6.7 mm
Cable diameter, min.	7.3 mm	Cable length	5 m
Conductor O.D.	-	Connection cross-section	2 x 0.34 + 2 x 0.22
Contact material	Ni/Au	Contact surface	Gold-plated
Contact tube diameter	M12	Material	PUR/ TPE
No. of poles	5	Pollution severity	3
Protection degree	IP 67	Rated voltage	30 V
Sheathing colour	black	Temperature range of housing	-25...+85 °C
Type of connection	Socket	jumpered	No

Classifications

ETIM 2.0	EC000304	ETIM 3.0	EC001855
UNSPSC	26-12-16-13	eClass 4.1	27-06-00-00
eClass 5.1	27-06-91-90	eClass 6.0	27-06-03-07
eClass 7.0	27-06-91-90		