





| SWITCH FUNCTION |          |
|-----------------|----------|
| POS. 1          | POS. 2   |
|                 |          |
| ON              | (ON)     |
| 1-3, 4-6        | 1-2, 4-5 |

(ON) = MOMENTARY



- NOTE:
1. ALL DIMENSIONS IN MM [INCH]
  2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
  3. TERMINAL NUMBERS FOR REF ONLY
  - ▲ 4. CONTACT MATERIAL: SILVER
  5. RATING: 2A 48VDC
  6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
  7. INSULATION RESISTANCE: 1,000 MΩ MIN.
  8. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
  9. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
  10. OPERATING TEMP.: -20°C to 55°C
  11. ▲ DENOTES CRITICAL PARAMETER.
  12. LAMP VOLTAGE: 12V
  - ▲ 13. ILLUMINATION COLOR: GREEN
  14. HARDWARE SUPPLIED: O-RING AND HEXNUT
  - ▲ 15. INGRESS RATING: IP40
  16. 2002/95/EC (ROHS) COMPLIANT



TITLE PV3F2H0NN-334

SCALE 1.5:1

DATE 1/25/2012

DR BMA

DWG 52-PV3F2H0NN334

REV D

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

|     |        |                               |          |     |
|-----|--------|-------------------------------|----------|-----|
| D   | 20452  | CORRECT CONTACT CONFIGURATION | 02/02/12 | BMA |
| C   | 20423  | UPDATE AND CONVERT            | 01/25/12 | BMA |
| REV | PCR NO | DESCRIPTION                   | DATE     | BY  |