

P9 Grab Handle

Folding · Surface mount



519

- Low profile folding style
- Concealed installation
- Anti-rattle friction feature

Material and Finish

Handle and base:

Aluminum, anodized, clear or black

Roll pin, mounting nuts and

lockwashers:

Stainless steel passivated

Bushing: Nylon

Performance Details


Maximum static load:

Internal threaded version

600 N (135 lbf)

External thread version

400 N (90 lbf)



Installation Notes

Internal thread:

Screws not supplied.

Calculate screw length using the following formula:

Door thickness + 5 (.20)

Maximum tightening torque of

mounting screws: 1.7 N·m

(15 in·lbf)

External thread:

Maximum door thickness 8.4 (.33)

Mounting nuts supplied.

Maximum tightening torque of nuts:

11.5 N·m (10 in·lbf)

Part Number Selection

For visual identification:


M4 products have a counterbored hole.

8-32 products have a countersunk hole

Other options available. For complete details on variety, part numbers, installation and specification, go to



www.southco.com/P9



P9 - C - 40 - T B - 1 F - P

C Centers

040 40 (1.57) Hole centers

064 64 (2.52) Hole centers

096 96 (3.78) Hole centers

128 128 (5.04) Hole centers

T Thread

08 Imperial 8-32

M4 Metric M4 x 0.7

B Base type

N Internal thread

X External thread

P Packing option

Omit for individual packaging (1 per bag)

3 Layer packaging contact Southco

F Finish

1 Clear anodized

5 Black anodized