

- RoHS COMPATIBLE, NOTE 6.
- PACKAGING OPTIONS, NOTE 3.

PLATING:

1= 0.76μm GOLD/GXT ON CONTACT AREA, 2μm TIN MIN ON TAILS

4= 2.0μm TIN MIN FULL PLATED

5= 0.25μm GOLD/GXT ON CONTACT AREA, 2μm TIN MIN ON TAILS

8= 0.38μm GOLD/GXT ON CONTACT AREA, 2μm TIN MIN ON TAILS

1.27μm NICKEL MIN UNDERLAYER FOR ALL PLATING VERSIONS

1.27 $\mu$ m NICKEL MIN UNDERLAYER FOR ALL PLATING VERSIONS

NOTES:

1. HOUSING MAT'L : HIGH TEMPERATURE THERMOPLASTIC. U194V-0 COLOR: BLACK
2. PIN MATERIAL : PHOSPHOR BRONZE
- 3 - PACKAGING OPTIONS:

= POLY BAGS  
B = TUBE + CAP  
A = TAPE & REEL WITH CAP, SEE TA840  
FOR PRODUCT AVAILABILITY.

4. 9N MIN RETENTION IN EITHER DIRECTION
5. TO DETERMINE DIMENSIONS :  
N = NUMBER OF POSITIONS PER ROW  
EXAMPLE : 8 POS N x 2.54 = 20.32mm
6. ROHS COMPATIBLE PRODUCT SPECIFICATIONS

Q - PLATING:



- "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.

b – MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 30 SECONDS IN A CONNECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.

C – LABELING:

- MEETS PACKAGING SPECS AS PER GS-14-920
- LEGAL STATEMENT: SEE GS-47-0004



| mat'l. code |          | surface   | tolerance |
|-------------|----------|-----------|-----------|
| ltr         | ecm no   | dr        | dte       |
| R           | B189883  | LWU       | 14.10.03  |
| S           | B-20587  | AMA       | 15.03.30  |
|             |          | dngles    |           |
|             |          | linear    |           |
|             |          | x.xx ±0.3 |           |
|             |          | x.xx ±0.5 |           |
| L           | F08-0206 | JOC       | 08.07.25  |
| M           | F09-0233 | JOC       | 09.12.24  |
| N           | F11-0097 | JOC       | 11.09.01  |
| P           | F11-0328 | LWU       | 11.11.15  |
| sheet       |          | revision  |           |
| index       |          | sheet     |           |
|             |          | dppd      | JMC       |
|             |          | COMPAGNON |           |
|             |          | 99.04.12  |           |
|             |          | 99.04.12  |           |