


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [112013-0003](#)
Status: **Active**
Overview: Brad® PC Network Interface Cards (NIC)
Description: PC104-DPIO PROFIBUS-DP Master/Slave 12 Mbps, PC/104 bus, HE13 connector

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Network Interface
Series	112013
Application	IO Control
Approvals	CE certified
Communication Speed	Profibus: 9.6 kbps to 12 Mbps
Messaging	Profibus* DP V0 Master, Profibus* DP V0 Slave, Profibus* DP V1 Master
Mounting Style	PC Slot
Operating System	Windows 7, Windows 8, Windows Server 2003, Windows Server 2008, Windows Vista, Windows XP
Overview	Brad® PC Network Interface Cards (NIC)
Product Name	applicom®
Protocol	Profibus*
Slot	PC/104
Software Downloads	DRL-DPM-104
Type	Profibus* Card
UPC	78678895474
Physical	
Channels	1
Interface	DAServer, DDE Server, DLL, OPC DA Server
Net Weight	300.000/g
Network Connection Type	HE13 (2 by 5 pins), Profibus* D-Sub Female (9 pin)
Packaging Type	Individual Carton
Processor	AMD SC520
Temperature Range - Operating	0°C to +65°C
Electrical	
Current - Maximum Input	5.5W
EMC	EN 55022 Class B, EN 61000-3-2, EN 61000-3-3, IEC 61000-6-2
Supply Voltage	5V
Material Info	
Old Part Number	DRL-DPM-104
Reference - Drawing Numbers	
Sales Drawing	SD-112011-0008



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[112013Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[112013-0003](#)