

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301050065](#)
Status: **Active**
Overview: [Specialty Lighting](#)
Description: Watertite Wet Location 100W Spotlight with In-line Transformer, Switch Screw Release Guard, 14/2 SOOW, Overall Length 7.62m (50.0')

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR85374

General
Product Family Portable Lighting
Series [130105](#)
NEMA Configuration NEMA 5-15
NEMA Rating NEMA 4X
Outlet None
Overview [Specialty Lighting](#)
Product Name Watertite
Type Hand Lamps, Specialty Light
UPC 78678861573

Physical
Cord Length - Primary 3.04m (10.0')
Cord Length - Secondary 15.24m (50.0')
Depth N/A
Duty Wet Location
Guard Included Yes
Guard Type Screw Release
Height 127.00mm (5.000")
Length 228.60mm (9.000")
Material - Guard #10 Gauge Vinyl Coated Steel
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical
Bulb Type Quartz Halogen
Cord Type - Primary 16/3 SOOW
Cord Type - Secondary 14/2 SOOW
Lamp Type PAR36
Lamp Wattage - Maximum 100W
Lumens 1000
On/Off Switch Yes
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info
Engineering Number 1691-12BS



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130105](#) Series