

Distributed by:


JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242


The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 19141

2012J-C (close type) 7600A-R



SEC A-A



NOTES

1.MATERIAL

1.1 Insulator:PBT+15% G.F. UL-94V-0

2.SPECIFICATION

2.1 Current Rating: 3Amp

2.2 Dielectric Withstading : AC 500V/min.R.M.S.

2.3 Insulator Resistance: 1000M ohms Min

2.4 Contact Resistance: 20m ohms Max

2.5 Operation Temperature: -55 °C to +85 °C

2.6 Contact retention force: 0.91 kg MIN.

2.7 Insertion force: 420g MAX. per contact.(pin gauge SQ. 0.64mm)

2.8 Withdrawal force: 28g MIN.per contact.(pin gauae SQ. 0.64mm)

REV.	NOTES	DATE
A	RELEASED	2005/10/15
B	增加料號:AMJ+P060A-59	2005/12/12
C	增加料號:AMJ+B060A-R91	2005/12/19

ORDER INFORMATION

Part No.	Color	Contact	Plating
AMJ+P060A-09	Black	Phosphor Bronze	Gold/Nickel Plated
AMJ+P060A-Y9	Yellow	Phosphor Bronze	Gold/Nickel Plated
AMJ+B060A-09	Black	Brass	Gold/Nickel Plated
AMJ+B060A-QP	BLUE	Bronze	Gold/Nickel Plated
AMJ+B060A-99	White	Brass	Gold/Nickel Plated
AMJ+B060A-R2	Red	Brass	Gold/Nickel Plated
AMJ+P060A-R2	Red	Phosphor Bronze	Gold/Nickel Plated
AMJ+P060A-59	Green(3285c)	Phosphor Bronze	Gold/Nickel Plated
AMJ-B060A-R91	Red(192U)	Brass	Gold/Nickel Plated

(ROHS)

單位(UNITS)	mm	Top Willing Co., Ltd.					
數量(QT'Y)	N/A						
材料(MT'L)	SEE NOTE						
處理(FINISH)	SEE NOTE						
繪圖(DRAW)		圖名(NAME)					
設計(DE'N)		MJ 6A黑磷銅半面金 無毒					
審校(CH'K)		料號(PART NUMBER)		AMJ+X060A-XX			
核准(APP'D)		圖號(DRAW NUMBER)		RAMJP060A09			
		圖檔(FILE NAME .DWG)		E:GCT/A/MJ/060			
		比例(SCALE)	1/1	圖紙(SIZE)	A4	頁次(SHEET)	1
						版次(REV.)	C

DIMENSIONS TOLERANCE
METRIC
.0= ±.20
.00= ±.10
.000= ±.0XX
.0000=±
ANG.= ± 2°