



Products

Search By:

Enter Molex Part No.

- Products
- New
- Contact Us
- About Us
- Investors
- Jobs
- Languages
- 日本語
한국어
简体中文

- English
中文显示
- Español
日本語
- Français
한국어
- Italiano
- Deutsch
- Português
- По Русски



Datasheet
Crimp Terminals

[[Home](#) > [Products](#) > [Crimp Terminals](#) > [Datasheet](#)]

50394-8100

Milli-Grid™ Crimp Terminal, Bag, 0.38µm (15µ") Select Gold


[View all parts in series 50394](#)

[E-mail this page](#)

[Samples](#)

[Buy](#)

Status	Active
Product Name	Milli-Grid™
Molex Series	50394
Gender	Female
Wire Size [AWG]	24, 26, 28, 30
Wire Insulation Diameter	1.40mm (.055") max.
Packaging	Bag
PHYSICAL	
Contact	Phosphor Bronze (CuSn)
Plating Contact	Gold (Au) Selective
Plating Thickness	0.38µm (15µ")
REFERENCE	
Designed In	Millimeters
Pitch / Center Spacing	2.00mm (.079")
990 Catalog Page	A-4
MX01 Catalog Page	B-5



This part is **ELV** and **RoHS COMPLIANT**

ENVIRONMENT

[RoHS Compliant](#) Yes

Features and Benefits

- Early entry terminal design for superior contact

Related Products

APPLICATION TOOLING		
Region	Description	Product Number
Americas	Hand Crimper	11-01-0204
Europe	Parallel Action Handtool for 50394 Terminals, 24-30 AWG	69008-0959