

Wera Kraftform® Plus Series 300

With a multi-component Kraftform® handle for demanding applications.

335 Slotted Screwdriver



Application: For slotted screws
Blade: Round, mat nickel
Tip: DIN 5264-A, ISO 2380, Lasertip®
Handle: Kraftform® with anti-roll protection, multi-component

Code	mm	mm	mm	mm	mm	mm	mm	mm	mm
05008006001 ¹⁾	0,4	2,0	60	70	2,5	5/64"	2 3/8"	10	
05110000001 ¹⁾	0,4	2,5	60	70	2,5	3/32"	2 3/8"	10	
05008007001 ¹⁾	0,4	2,5	75	70	2,5	3/32"	3"	10	
05008008001 ¹⁾	0,5	3,0	150	81	4,0	1/8"	6"	10	
05008009001 ¹⁾	0,5	3,0	200	81	4,0	1/8"	8"	10	
05110001001 ¹⁾	0,5	3,0	80	81	3,0	1/8"	3 1/8"	10	
05008015001	0,6	3,5	100	81	3,5	9/64"	4"	10	
05110002001	0,6	3,5	125	81	3,5	9/64"	5"	10	
05110003001	0,6	3,5	200	81	3,5	9/64"	8"	5	
05110004001	0,8	4,0	100	98	4,0	5/32"	4"	10	
05110005001	0,8	4,0	150	98	4,0	5/32"	6"	10	
05110006001	0,8	4,0	200	98	4,0	5/32"	8"	5	
05008027001 ¹⁾	0,8	4,0	300	98	4,0	5/32"	12"	2	
05110007001	1,0	5,5	125	98	5,5	7/32"	5"	10	
05008055001	1,0	5,5	150	98	5,5	7/32"	6"	10	
05110008001	1,0	5,5	200	98	5,5	7/32"	8"	5	
05008060001 ¹⁾	1,0	5,5	300	98	5,5	7/32"	12"	2	
05008061001	1,2	6,0	100	105	6,0	5/16"	4"	10	

¹⁾ without Lasertip®

334 Slotted Screwdriver



Application: For slotted screws
Blade: Round, mat nickel
Tip: DIN 5264-A, ISO 2380, Lasertip®
Handle: Kraftform®, with anti-roll protection, multi component
Sizes: 2.0 x 12.0; 2.5 x 14.0: material = Weralit® II, one component

Code	mm	mm	mm	mm	mm	mm	mm	mm	mm
05007610001 ¹⁾	0,8	5,0	100	98	5,0	3/16"	4"	10	
05007620001 ¹⁾	1,0	6,0	125	105	6,0	15/64"	5"	10	
05340330001	1,0	6,0	150	105	6,0	1/4"	6"	10	
05110010001	1,2	6,5	150	105	6,0	1/4"	6"	10	
05007621001	1,2	7,0	150	105	7,0	9/32"	6"	5	
05007635001 ¹⁾	1,2	7,0	150	105	7,0	9/32"	6"	10	
05110011001	1,2	8,0	175	112	7,0	5/16"	7"	5	
05007640001	1,2	8,0	175	112	7,0	5/16"	7"	5	
05110104001	1,6	10,0	200	112	9,0	3/8"	8"	5	
05110105001 ²⁾	2,0	12,0	250	117	10,0	1/2"	10"	2	
05018274001 ^{2,3)}	2,5	14,0	250	117	-	1/4"	8"	2	

¹⁾ These sizes are not included in standard specifications.

²⁾ without Lasertip®

³⁾ Identical with item 932 A, pound-thru hexagon blade, impact cap, hexagon bolster.

334 SK Slotted Screwdriver



Application: For slotted screws
Blade: Hexagonal, with bolster from 0,8 x 4,5, mat nickel
Tip: DIN 5264-A, ISO 2380, Lasertip®
Handle: Kraftform®, multi-component

Code	mm	mm	mm	mm	mm	mm	mm	mm	mm
05007670001	0,6	3,5	4	0	75	81	9/64"	3"	10
05007671001	0,8	4,0	4	0	90	81	5/32"	3 1/2"	10
05007672001	0,8	4,5	5	8	90	98	0,178"	3 1/2"	10
05007673001	1,0	5,5	6	10	100	98	7/32"	4"	10
05007674001	1,2	6,5	6	10	125	105	1/4"	5"	10
05007675001	1,2	7,0	6	10	125	105	9/32"	5"	10
05007676001	1,6	9,0	8	13	150	112	11/32"	6"	10
05007677001	1,6	10,0	8	13	175	112	3/8"	7"	5

378 B Slotted Screwdriver



Application: For slotted screws
Blade: Square, mat nickel
Tip: DIN 5264-A, ISO 2380, Black Point
Handle: Kraftform®, with anti-roll protection, multi component; size: 2,5 x 14,0 x 225: material = Weralit® II, one-component

Code	mm	mm	mm	mm	mm	mm	mm	mm	mm
05110050001	0,8	4,0	4	75	98	5/32"	3"	10	
05110051001	1,0	5,5	5	100	98	7/32"	4"	10	
05110052001	1,2	6,5	6	125	105	1/4"	5"	10	
05110053001	1,6	8,0	8	150	112	5/16"	6"	10	
05007355001	1,6	10,0	8	60	112	3/8"	2 3/8"	5	
05110054001	1,6	10,0	8	175	112	3/8"	7"	5	
05110150001	1,6	10,0	8	200	112	3/8"	8"	5	
05007360001	1,6	10,0	8	600	112	3/8"	24"	5	
05110055001	2,0	12,0	10	200	112	1/2"	8"	5	
05110151001	2,0	12,0	10	250	112	1/2"	10"	5	
05110056001	2,5	14,0	12	225	117	9/16"	9"	2	