



395 Handheld Refractometer

APPLICATIONS

HVACR:

- Radiant Heat Line Fluids For walkways, garages, closed loop systems, and in-floor systems

AUTOMOTIVE:

- Engine coolants
- Battery fluid condition
- Recreational vehicles

PLUMBING:

- Battery condition of sump pump battery back up systems

Turn over for
technical
information
and accessory
part numbers.

The
Value
Leader™

The 395 Handheld Refractometer

is designed to give an accurate reading regarding the freezing point of fluids used in hydronic heating systems. It is quick and easy to use. Place a drop of fluid on the prism, close the plastic lid, and look through the eye piece. Where the blue and white colors meet indicates the freezing point of the coolants or the state of charge for batteries.



FEATURES

- Use to test the following liquids:
 - Propylene glycol
 - Ethylene glycol
 - Battery fluid
- Does not degrade like litmus paper; Allows for more accurate readings
- Easy viewing: cushioned eye piece adjusts to most visual needs.
- Smooth focus adjustment for reliable repeat testing

The above information is provided to the best of TPI's knowledge and is not guaranteed.
The above information is subject to change at any time.

visit us at www.tpi-thevalueleader.com



TECHNICAL SPECIFICATIONS AND ACCESSORIES

- Digital Multimeters
- Clamp Meters
- Hand-held Oscilloscopes
- Refrigerant & Combustible Gas
- Leak Detectors
- Temperature Testers
- BNC
- Coax Cable Connectors
- Test Leads
- Accessories

Test Products International, Inc.

Headquarters:
9615 SW Allen Blvd.
Beaverton, OR 97005
USA
503-520-9197
Fax: 503-520-1225
email:
info@tpi-thevalueleader.com

Test Products International, Ltd.

342 Bronte St. South
Unit 9
Milton, Ontario L9T
5B7
Canada
905-693-8558
Fax: 905-693-0888
email:
info@tpicanada.com

Test Products International UK Ltd.

Longley House, East Park
Crawley, West Sussex
RH10 6AP England
Tel: +44 (0)1293 561212
Fax: +44 (0)1293813465
contactus@tpieurope.com

395 Handheld Refractometer

395 SPECIFICATIONS

Calibration	Field calibrateable using distilled water
Liquid and Range	Propylene Glycol: -60°F to 20°F (-50°C to -5°C) Ethylene Glycol: -60°F to 20°F (-50°C to -5°C) Battery Fluid: 1.10 to 1.4 pH with recharge, fair, and good ratings
Dimensions	6 3/8" x 1 1/4", 7/8" tube diameter
Weight	.6lbs (.286kg)
Standard Accessories	Refractometer Calibration screwdriver Eyedropper Distilled water Protective plastic case

TDS / Salt Meter 390



- Test condensate water in cooling tower and humidifier reservoir applications to prevent bacterial growth
- Test TDS levels in make-up water to prevent scale formation, corrosion, and embrittlement
- Reduce water and chemical consumption in boilers and cooling towers
- Determine when to perform blowdown and add make-up water
- Prevent contamination and corrosion of control valves, heat exchangers, and steam traps
- Verify automated TDS controllers are functioning properly
- Prevent low quality wet steam generation in boilers due to foaming caused by high TDS levels

Distributed By:



To learn about the entire
line of TPI products visit:

www.tpi-thevalueleader.com

L 395-0107

Copyright © 2007 Test Products International, Inc.