



Sales Outline Drawing

Revision

A**Specifications:**

Oscillation Frequency (Hz)	2400 $\pm$ 250
Operating Voltage (Vpp)	4.5 ~ 5.5
Rated Voltage (Vpp)	5.0
Current Consumption Max. (mA)	50 at Rated Voltage
Sound Pressure Level (dB/min)	85 at 10cm at Rated Voltage
Coil Resistance (Ω)	45 $\pm$ 5
Operating Temperature ($^{\circ}$ C)	-20 ~ +70
Storage Temperature ($^{\circ}$ C)	-30 ~ +80
Lead Pin	Tin Plated Brass
Housing	PPO plastic resin (Color: Black)
Weight (Grams)	1.6
Condition by wave soldering ($^{\circ}$ C)	245 $\pm$ 5 / 3 $\pm$ 0.5 sec
Condition by hand soldering ($^{\circ}$ C)	350 $\pm$ 20 / within 5 sec
Options	For other options contact factory

PS: Vp-p = 1/2duty, square wave

RoHS Compliant**Dimensions:** (units: mm)**Recommended Driving Circuit:**

The base current I_b should be high enough so that it saturates the collector current of the transistor with the CB load.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[PB-1224PE-05Q](#)