


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS				DOC. NO.	SPC-FD05	Effective:	12/21/98	Doc No.	880
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
170	A	RELEASED	SAS	07/21/99	JC	2/2/00	DJC	4/5/00	



- SPECIFICATIONS:**
1. DO-IT-YOURSELF Ø4mm RETRACTILE SLEEVE STACKING BANANA PLUG, BUTTON ATTACHMENT.
 2. INSULATOR BODY: POLYACETAL
 3. PLUG BODY: BRASS, NICKEL PLATED
 4. CONTACT SPRING: BECU, NICKEL PLATED
 5. VOLTAGE: 500V
 6. CURRENT: 36A MAX.
 7. TEMPERATURE: -20 °C TO +80 °C
 8. CONDUCTOR: SIZE Ø.090 (12AWG)
 9. INSULATION: Ø.156
 10. STRIP LENGTH: .25 (6.4)