

F

E

D

C

B

A

F



E

D



C

B

A



SECTION A-A



注記 NOTES

1. 使用材料 MATERIAL

ハウジング : 液晶ポリマー (LCP) UL94V-0 (黒)
HOUSING: LIQUID CRYSTAL POLYMER UL94V-0 (COLOR: BLACK)

ターミナル : 銅合金
TERMINAL : COPPER ALLOY

金具 : 銅合金
FITTING NAIL : COPPER ALLOY

2. メッキ仕様 PLATING

ターミナル TERMINAL

金メッキ
GOLD

下地メッキ : ニッケルメッキ
UNDER PLATING : NICKEL

※コンタクト部とテール部はニッケルメッキによって分断されている金メッキです。
DIVIDE INTO PARTS THE GOLD PLATING OF THE CONTACT
AND THE TAIL PART BY THE NICKEL PLATING.

金具 FITTING NAIL

金メッキ (テール部のみ)
GOLD (ONLY TAIL PART)

下地メッキ : ニッケルメッキ
UNDER PLATING : NICKEL

△ (全極数 / 2) = 偶数の場合に適用。
APPLY FOR (CIRCUIT / 2) = EVEN.

4. 嵌合相手 : 504011 シリーズ
MATE WITH : 504011 SERIES.


5. テール平坦度は、 0.08 以下

テール及び金具の平坦度は、 0.1 以下
TAIL COPLANARITY TO BE 0.08 MAXIMUM.
TAIL AND FITTING NAIL COPLANARITY TO BE 0.1 MAXIMUM.

6. ELV & RoHS 適合品
ELV and RoHS COMPLIANT.

1.4	3.95	504008-1010		10
B	A	EMBOSSED PACKAGE		極数 CIRCUITS
		オーダー番号 ORDER No.		
		CONNECTOR SERIES No. : 504008-**09		

RELEASED EC NO: J2013-0281 DRWN: TANI GUCHI 01 2012/09/04 CHKD: RTAKEUCHI 2012/09/04 APPR: MSASAO 2012/09/05	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 15:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± ---	DRAWN BY TANI GUCHI 01	DATE 2012/09/04	TITLE 0.35 B-TO-B CONN HGT=0.7 REC ASSY 035ST7				
		10 OVER 30 UNDER	± ---	CHECKED BY RTAKEUCHI	DATE 2012/09/04					
		30 OVER	± ---	APPROVED BY MSASAO	DATE 2012/09/05					
		ANGULAR	±1 °	MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-504008-001		1 OF 2			
REV A		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								




RECOMMENDED P.W. BOARD
PATTERN LAYOUT

RELEASED EC NO: J2013-0281 DRWN: TTANIGUCHI 01 2012/09/04 CHKD: RTAKEUCHI 2012/09/04 APPR: MSASAO 2012/09/05 A	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 15:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
		10 UNDER	± ---	DRAWN BY TTANIGUCHI	DATE 01 2012/09/04	TITLE 0.35 B-TO-B CONN HGT=0.7 REC ASSY 035ST7			
		10 OVER 30 UNDER	± ---	CHECKED BY RTAKEUCHI	DATE 2012/09/04				
		30 OVER	± ---	APPROVED BY MSASAO	DATE 2012/09/05				
		ANGULAR ±1 °		MATERIAL NO. SEE CHART		DOCUMENT NO. SD-504008-001			SHEET NO. 2 OF 2
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

注記 NOTES


- 製品詳細寸法については製品単体図面を参照下さい。
RE DETAILED DIMENSION, SEE PRODUCT DRAWING.
- 梱包数量：3000 個／リール
NUMBER OF CONNECTORS：3000PCS/REEL
- リードテープ長さ LEAD TAPE LENGTH



- トップテープの剥離強度：0.1N~1.3N(10gf~130gf)
(剥離方向は下図参照)
尚、本規格値は出荷時に適用。(但し、輸送時に剥離が発生しないこと。)
PEELING OFF FORCE OF TOP TAPE：0.1N~1.3N(10gf~130gf)
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)
THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT.
PEEL OFF SHOULD NOT BE ALLOWED, DURING TRANSPORTION.



- 材料 MATERIAL
キャリアテープ (CARRIER TAPE)：ポリスチレン (POLYSTYRENE)
トップテープ (TOP TAPE)：PET, OTHER
リール (REEL)：ポリスチレン (PS) <リサイクル材を含む>
POLYSTYRENE (PS) <RECYCLE MATERIAL CONTAINED>
- ELV 及び RoHS適合品
ELV AND RoHS COMPLIANT



RELEASED EC NO: J2012-1336 DRWN: TTANIGUCHI 2012/04/17 CHKD: RTAKEUCHI 2012/05/16 APPR: MSASAO 2012/05/17	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	MODEL NO. SD-504008-002		THIRD ANGLE PROJECTION	
		10 UNDER	± ---	DRAWN BY TTANIGUCHI	DATE 2012/04/17	TITLE 0.35 B-T0-B CONN HGT=0.7 REC. ASSY EMBSTP PKG 035ST7					
		10 OVER 30 UNDER	± ---	CHECKED BY RTAKEUCHI	DATE 2012/05/16						
		30 OVER	± ---	APPROVED BY	DATE						
		ANGULAR ±1 °		MATERIAL NO.		DOCUMENT NO.					SHEET NO.
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-504008-002				1 OF 2		
	REV A			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

10

9

8

7

6

5

4

3

2

1

F




E

D

C

B

A



16	21.4	17.4	4.07	504008-1010	10
キャリアテープ幅 CARRIER TAPE WIDTH	C	B	(A)	MATERIAL No.	CKT.
				MODEL No.	504008-**10

RELEASED EC NO: J2012-1336 DRWN: TTANIGUCHI 2012/04/17 CHKD: RTAKEUCHI 2012/05/16 APPR: MSASAO 2012/05/17 A	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
		10 UNDER ± ---		DRAWN BY DATE TTANIGUCHI 2012/04/17		TITLE 0.35 B-T0-B CONN HGT=0.7 REC. ASSY EMBSTP PKG 035ST7 molex		
		10 OVER 30 UNDER ± ---		CHECKED BY DATE RTAKEUCHI 2012/05/16				
		30 OVER ± ---		APPROVED BY DATE				
	REV	ANGULAR ±1 °		MATERIAL NO. SEE CHART		DOCUMENT NO. SD-504008-002		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

9

8

7

6

5

4

3

2