

Glass and tile drills with carbide cutting edge and straight shank

Cutting edge: special tungsten carbide plate polished
Soldering: high-performance special soldering
Shank: straight shank
Right-hand cutting

Best results with lower r.p.m. and good cooling with water, vinegar, turpentine and kerosine.

Especially suited for drilling of window pane, mirror glass, bottles, porcelain, tiles, ceramics etc.

Packing unit: in plastic bags of 1



Ø mm	Ø inch	Shank-Ø mm	Total length mm	Article no.	Price / each €
3,0	1/8	3	58	223 003	
4,0	5/32	3	58	223 004	
5,0	3/16	4	58	223 005	
6,0	15/64	5	58	223 006	
8,0	5/16	6	78	223 008	
10,0	25/64	6	98	223 010	
12,0	15/32	8	98	223 012	



2.6

SDS-plus hammer drill set in steel case

Description	Article no.	Price / set €
7-piece set Ø 5 - 6 - 8 x 110 mm Ø 6 - 8 - 10 - 12 x 160 mm	205 246	



Concrete drill set in steel case

Description	Article no.	Price / set €
7-piece set Ø 4 x 75 mm - 5 x 85 mm - 6 x 100 mm - 6 x 100 mm Ø 8 x 120 mm - 10 x 120 mm - 12 x 150 mm	205 255	



Percussion drill set in steel case

Description	Article no.	Price / set €
7-piece set Ø 4 x 75 mm - 5 x 85 mm - 6 x 100 mm - 6 x 100 mm Ø 8 x 120 mm - 10 x 120 mm - 12 x 150 mm	205 256	

