


DESCRIPTION: 25 POS MICRO-D FEMALE (ASSEMBLED) TO BLUNT CUT



1. P1: NORCOMP MICRO D 25S, ASSEMBLED HOOD W/THUMBSCREWS
2. P2. BLUNT CUT END
3. WIRE: 28AWG [7X36] x25C +ALUMINUM FOIL + BRAID 65%, UL2464, COLOR BLACK
4. PINOUT:

P1	P2
1	BLACK
2	BROWN
3	RED
4	ORANGE
5	YELLOW
6	GREEN
7	BLUE
8	VIOLET
9	GRAY
10	WHITE
11	PINK
12	LIGHT GREEN
13	BLACK WHITE
14	BROWN WHITE
15	RED WHITE
16	ORANGE WHITE
17	GREEN WHITE
18	BLUE WHITE
19	VIOLET WHITE
20	RED BLACK
21	ORANGE BLACK
22	YELLOW BLACK
23	GREEN BLACK
24	GRAY BLACK
25	PINK BLACK
SHELL	DRAIN

CCA-025-YYR152
I = INCHES ———— LENGTH
F = FEET
M = METERS

EXAMPLES:
CCA-025-I18R152 = 18 INCHES
CCA-025-F03R152 = 3 FEET
CCA-025-M01R152 = 1 METER

PACKAGED: 1 PER BAG

RoHS COMPLIANT

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: P. JENKINS		DATE: 01-18-12		
		CHECKED:		DATE:		
	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	SCALE: NTS		SHEET OF 1 1		REV 0
		DWG NO. CCA-025-YYR152				