

WIRE FERL UNINSUL

Non-Insulated Wire Ferrules



Cat No: 73/10VZ

UPC No: 783310050124

Description

- For terminating stranded wire into terminal blocks
- Electrolytic copper and tin plating provide maximum conductivity and low contact resistance
- Meets DIN 46228, part 1, 0.5 - 50 mm²

Specifications

- Color Code : DIN 46228, Part 1
- Finish : Tin Plated
- Material : Electrolytic Copper
- Recommended Crimping Tools : K1GL, K32GL, K36GL, K30GL, Die 03283
- Size : 0.394 IN (10.000 MM) Overall Length
- Standard : RoHS
- Type : Non Insulated
- Wire Size : 14 AWG (2.500 SQ-MM)
- Wire Type : Stranded