

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [07-01-8101](#)
Status: **Active**
Description: Commoning Crimp Housing Receptacle Housing, 10 Circuits

Documents:
[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series [1461](#)
Application Power
Comments Circuit are Labeled with Ink Stamped Numbers
Product Name Commoning Connector
UPC 800753755260

Physical

Circuits (maximum) 10
Circuits Detail Circuits Labeled 1-5
Color - Resin Black
Flammability 94V-0
Gender Female
Glow-Wire Compliant No
Keying to Mating Part None
Lock to Mating Part None
Material - Resin Polyester
Net Weight 12.625/g
Number of Rows 1
Packaging Type Bag
Panel Mount Yes
Pitch - Mating Interface 4.45mm
Pitch - Termination Interface 4.45mm
Polarized to Mating Part Yes
Ports 1
Temperature Range - Operating -40°C to +105°C

Electrical


Current - Maximum per Contact 12A

Material Info

Old Part Number 1461-10E

Reference - Drawing Numbers

Sales Drawing SD-1461-*



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[1461Series](#)