




NOTES:


1. SUGGESTED MOUNTING HOLE = Ø.177
2. HARDWARE IS INCLUDED

LEAD FINISH:	SOLDER
BUSHING FINISH:	SILVER
CAPACITANCE	2000pF MIN
TEMP. RANGE	-55°C TO 125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE	125°C 115 VAC MAX. 125°C 200 VDC MAX.
D.C. RESISTANCE	.01ohms MAX.

NO LOAD INSERTION LOSS:

FREQ	IL
10MHz	8dB
100MHz	48dB
1GHz	70dB

SCHEMATIC



MARKING:

PART: S000 (FAIRVIEW)
S000M (MEXICO)

PACKAGE: SCI-3223-000

DATE CODE

QTY/BAG (200 MAX.)



	8	7	6	5	4	3	2		REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	 ERIE, FAIRVIEW PENNSYLVANIA SPECTRUM CONTROL INC.
									CHANGE NOTICE	Fractions ± 1/64	
										Dec. .xx±	
										Dec. .xxx±.010	
										Angles ±0° 30'	
										CODE IDENT. NO.	Dwn. SLAGLE Date 5/21/01 Engr. T. Taylor Scale NONE
										DLSP2	Description Pi RESIN SEAL FILTER SCI-3223-000