

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART NUMBER		STUD SIZE	DIMENSIONS in.				
PREFIX	PK		A $\pm .020$	W $\pm .010$	C $\pm .015$	M $\pm .020$	H $\pm .010$
PV2-10RX	-XY -TY	#10	1.94 (.49.28)	.68 (.17.27)	.58 (.14.73)	1.60 (.40.64)	.20 (.5.08)
PV2-14RX	-XY -TY	1/4"	1.94 (.49.28)	.68 (.17.27)	.58 (.14.73)	1.60 (.40.64)	.27 (.6.86)
PV2-56RX	-XY -TY	5/16"	1.94 (.49.28)	.68 (.17.27)	.58 (.14.73)	1.60 (.40.64)	.33 (.8.38)
PV2-38RX	-XY -TY	3/8"	1.94 (.49.28)	.68 (.17.27)	.58 (.14.73)	1.60 (.40.64)	.39 (.9.91)
PV2-12RX	-XY -TY	1/2"	2.03 (.51.56)	.86 (.21.84)	.58 (.14.73)	1.60 (.40.64)	.52 (1.3.21)

NOTES:

1. UL LISTED FOR:
 - A. 600V MAX VOLTAGE RATING
 - B. 221° F (105° C) MAX TEMP RATING
 - C. #2 AWG STRANDED COPPER WIRE
2. PACKAGE QTY: STD. PKG. -X = 10
BULK PKG. -T = 200, -TY = 200
3. MATERIAL:
 - A. STAMPING - .060" (15.2) THK COPPER,
TIN PLATED
 - B. HOUSING - VINYL, RED
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
5. INSTALLATION TOOL: CT-720



LISTED
587H
E52164



A4 1220

										 PANDUIT CORP. TINLEY PARK, ILLINOIS			
										#2 BARREL VINYL INSULATED RING TONGUE .632 (16.05) MAX. WIRE INSUL. DIAMETER			
06	3-10	SB		Corrected UI file number									
REV	DATE	BY	CHK	DESCRIPTION		ECN#	QA	CUST	PM	DRAWN BY DAW	CHK'D	SCALE NONE	DRAWING NO. A41220