

Interruptor Type Opto Sensors



Download the 2010 Aleph Photosensors Data Book (12 MB PDF)
(Please note that with a dial up modem, downloading the specification sheet can take several minutes, during which time your browser will display a blank screen. To download the free Adobe Acrobat Reader, [click here](#))

Part Number	Output Type	Style (mm)	Features	Sensing slot width (mm)	Aperture width (mm)
OF- 11T - N23	-			-	-
OJ- 1001	IC	 H = 10 L = 13 W = 6	PCB mount Miniature High sensitivity	3.0	0.5
OJ- 111				5.0	
OJ- 121				5.0	
OJ- 141	Tr		Compact PCB direct mounting type (with a locating boss)	3.0	0.5
OJ- 161	Tr	 onlinecomponents.com THE ONLINE DISTRIBUTOR OF THE BEST COMPONENTS	PCB direct mounting type (with a locating boss)	5.0	0.5
OJ- 165	-			-	-
OJ- 171				5.0	
OJ- 211	-			-	-
OJ- 227	IC		Compact PCB direct mounting type (with a locating boss) High resolution	3	0.5
OJ- 231				5.0	
OJ- 261				5.0	
OJ- 235	-			5.0	-
OJ- 271	-			5.0	-
OJ- 275	-			5.0	-
OJ- 431	Tr		Dustproof One side mounting With wires	5	0.5
OJ- 451				5.0	
OJ- 461				5.0	
OJ- 535 - A5	-			-	-
OJ- 551 - A5				5.0	
OJ- 555 - A5				5.0	
OJ- 561 - A5				5.0	
OJ- 655 - A5	-			-	-