

Heatsinks f.cool

Cases f.case

Connectors f.con

Sockets

PCB connectors

Male headers

Female headers

Direct female connectors

Jumpers

IDC-connectors

D-Sub connectors

Brackets for PC

Optoelectronics

Male headers

SL 10 SMD ...

SL 10 SMD 062 7 S B SM

□ 0.635 mm, SMD-technique

... packing (option) - additions:

SL 10 SMD 040-104 ... SM; ... B SM: 4-20 contacts

SL 10 SMD 040-062 ... B TR: 4-20 contacts

SL 10 SMD 078 / 104 - 130 ... B TR: 4-12 contacts

Data sheet

add to request



Features

Technical Drawing

Equipping

Variants

Service

Accessories / related products

grid	2.54 mm
no. of contacts	7
contact material	CuSn alloy
surface of contact	selective gold-plated
surface contact /	Ni+≥0.2µm Au
contact sleeve	Ni+4...6µm Sn
version	male header
volume resistance	≤5 mΩ
nominal current	3 A
nominal voltage	250 V AC
test voltage	2000 V
insulating body material	PA 4.6. GF
temperature range	-40°C... +163°C (260°C/10 s)
class of inflammability	UL 94 V-0
specific insulation resistance	>10.0 ⁷⁰ Ω·m
connection type	SMD
reflow solderable	yes
packing	pick and place pad and bar magazine