



Cirrus 60



Cirrus 60		FGC 3000	FGC 3001
Nominal Power at 10°C	W	200 / 300 / 400	200 / 300 / 400
Nominal Input Voltage	V	230 VAC	115 VAC
Nominal Input Frequency	Hz	50	60
Operating Temperature Range	°C	-10 to +70°C	-10 to +70°C
Storage Temperature Range	°C	-40 to +70°C	-40 to +70°C
Fan Livetime (MTTF at 30°C)	h	329,447	329,447
Fan Volumetric Flow, approximate	m³/h	10	13
Weight, add 35 g for bracket	g	275	275
Dimensions	Cross section mm	71 x 70	71 x 70
	Length mm	96,5	96,5
Harness Length	mm	240	240
Ingress Protection, EN60529		IP 20	IP 20
Electrical Protection Class		II	II
Recommended Fuse, Time Delay	A	6,3	6,3
Recommended MCB Type B	A	6	6

Features:

- High power to size ratio
- Lightweight
- Easy to fit
- Three power settings
- Independent fan circuit to aid climate cooling

Options:

- FGB 300: 35mm DIN Rail clip (EN 50022)
- FGB 301: Side mounting bracket (4 x M4)
- FGB 302: Bulkhead mounting bracket (4 x M4)



Approvals pending

DBK Technitherm Ltd.

Components

Unit 11, Llantrisant Business Park
Llantrisant
Rhondda Cynon Taff, CF72 8LF
Wales, United Kingdom

Phone:
General + 44 (0) 14 43 23 79 27
Sales + 44 (0) 87 08 72 04 81
Fax: + 44 (0) 14 43 23 78 67

General: info@dbkt.co.uk
Sales: sales@dbkt.co.uk
Technical: technical@dbkt.co.uk