

329-P



#### General

Color: Grey  
 T&B UPC: 06739600866  
 T&B Status: M

#### Packaging Information

Packaging Format: Propak  
 Quantity per Package: 100  
 Std. Pkg. (Min/Mult): 1000 Units

#### Dimension Information

Wire Range: 22 to 16

# marrette®

The Marrette XTP is a high quality, twist-on wire connector with a unique spring and cap grip design that sets it apart from the competition. AWG wire range 22 to 16.

Model	Colour	AWG Wire Range							
		22	20	18	16	14	12	10	8
329	grey	Min.: 1 #22 + 1 #20	Max.: 2 #22 + 3 #20						
330	blue	Min.: 1 #22 + 1 #20	Max.: 3 #16						
331	orange			Min.: 2 #18	Max.: 3 #14				
333	yellow			Min.: 2 #18 + 1 #14	Max.: 2 #14 + 1 #10				
335	red	Min.: 1 #22 + 2 #10	Max.: 1 #14 + 4 #12						
822*	blue	Min.: 2 #22 + 1 #20	Max.: 2 #8						

#### Marrette Specifications

External Cap: - Made of tough, durable polypropylene and 105 degrees C-rated to withstand high installation pressures. - Posi-Grip surface combines a matte finish with closely-spaced, deep grooves for superior twisting power, even when hands are greasy or damp. - Deep, wide throat ensures full insulation coverage. - Threaded entry helps guide large wire bundles into the spring chamber. - Colour-coded for quick and easy size selection. - Inner Spring: - Exclusive Live Action variable volume spring expands to accommodate more wires with less twisting effort, compared to other connectors with a "fixed spring" design. - Round spring. - Unique copper-coated spring helps resist corrosion. - Approved for circuits up to 300V only. — For copper wire only. - Convenient packaging - sized right and job-site ready!