

## 48-Port 2U Rackmount Cat6 110 Patch Panel, 568B, RJ45 Ethernet

MODEL NUMBER: **N252-048**



### Highlights

- 19-in. rackmount ready
- EIA/TIA 2/32 spacing
- 2U ( 3.50" ) High
- 110 type punchdown termination
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Package Includes

- Cat6 Patch Panel 568B-48 Port

### Description

Tripp Lite's Category 6 Patch Panels offer you all the functionality and compatibility as any name brand. Each panel comes with 110-type termination, while meeting and exceeding EIA/TIA TSB-40 Category 6 connecting hardware specifications. Color coded for both EIA/TIA 568A & 568B installations. 48 ports ensure a wide range of plug-n-play options. The clear numbering on both the front and back of each panel gives you a quick and easy way to identify cable runs and the high density 19in wide, 2U High, panel design will save you valuable space in on the rack.

### Features

- Cat6
- UL approved
- Ports clearly numbered both on front and back
- Labels on front enable each port to be named
- Color coded label on back offers both EIA/TIA 568A & 568B wiring
- Metal frame
- EIA/TIA 2/32 spacing
- Rack mountable on a 19" rack ( 2U High )

### Specifications

General Info	
Product Group	PATCH PANELS & KEYSTONE JACKS
OVERVIEW	
Model Type	Patch Panels

<b>UPC ASSIGNMENT</b>	
Unit Carton UPC#	037332120045
<b>PHYSICAL</b>	
Color	Black
Style	Cat6/6e/6a
<b>CONNECTIONS</b>	
Connector A	110-TYPE TERMINAL (X48)
Connector B	RJ45 (FEMALE) (X48)
Connector C	(x12) RJ45 (Female)
Connector D	(x12) RJ45 (Female)
Ports	48
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.